



**Product:** [127937A](#)

DataTuff® 5e, 4 Bonded-Pr #24 Sol BC, PO Ins, OS, PO Jkt, AIA Armor, PVC Jkt

[Request Sample](#)

## Product Description

Industrial Ethernet Cat 5e, 4 Bonded-Pair 24AWG (Solid) Bare Copper, PO Insulation, Overall Beldfoil® Shield, PO Inner Jacket, Aluminum Interlock Armor, PVC Outer Jacket

## Technical Specifications

### Product Overview

Suitable Applications:	exposure to abrasion, burial, harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc. exposure to rodent, crush, or cut through force,
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

Element	AWG	Stranding	Material	No. of Pairs
Pair(s)	24	Solid	BC - Bare Copper	4

#### Insulation

<b>Material</b>	PO - Polyolefin
Bonded-Pair:	Yes

#### Color Chart

Color
White/Blue Stripe & Blue
White/Orange Stripe & Orange
White/Green Stripe & Green
White/Brown Stripe & Brown

#### Inner Jacket

Material	Nominal Diameter	Ripcord
PO - Polyolefin	0.237 in	Yes

#### Outer Shield

Type	Material	Material Trade Name	Coverage [%]
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%

#### Outer Jacket

Material	Nominal Diameter	Ripcord	Separator Material
PVC - Polyvinyl Chloride	0.600 in	No	Polyester Tape

### Construction and Dimensions

#### Armor

<b>Diameter over Armoring</b>
0.510 in

### Electrical Characteristics

## Conductor DCR

### Max. Conductor DCR

93.8 Ohm/km

## Capacitance

### Max. Capacitance Unbalance

330 pF/100m

## Delay

### Max. Delay Max. Delay Skew Nominal Velocity of Propagation (VP) [%]

538 ns/100m 45 ns/100m 70%

## High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. SRL (Structural Return Loss)	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2.0 dB/100m	65.3 dB	62.3 dB	63.3 dB	60 dB	63.8 dB	60.8 dB	20 dB	23 dB	100 ± 15 Ohm	102.5 ± 7.5 Ohm
4 MHz	4.1 dB/100m	56.3 dB	53.3 dB	51 dB	49 dB	51.7 dB	48.7 dB	23.6 dB	23 dB	100 ± 15 Ohm	102.5 ± 7.5 Ohm
8 MHz	5.8 dB/100m	51.8 dB	48.8 dB	46 dB	43 dB	45.7 dB	42.7 dB	25.4 dB	24.5 dB	100 ± 15 Ohm	101 ± 6 Ohm
10 MHz	6.5 dB/100m	50.3 dB	47.3 dB	43 dB	41 dB	43.8 dB	40.8 dB	26 dB	25 dB	100 ± 15 Ohm	101 ± 6 Ohm
16 MHz	8.2 dB/100m	47.3 dB	44.3 dB	39 dB	36 dB	39.7 dB	36.7 dB	26 dB	25 dB	100 ± 15 Ohm	101 ± 6 Ohm
20 MHz	9.3 dB/100m	45.8 dB	42.8 dB	36.5 dB	33.5 dB	37.7 dB	34.7 dB	26 dB	25 dB	100 ± 15 Ohm	101 ± 6 Ohm
25 MHz	10.4 dB/100m	44.3 dB	41.3 dB	33.9 dB	30.9 dB	35.8 dB	32.8 dB	25.5 dB	24.3 dB	100 ± 15 Ohm	101 ± 6 Ohm
31.25 MHz	11.7 dB/100m	42.9 dB	39.9 dB	31 dB	28 dB	33.9 dB	30.9 dB	25 dB	23.6 dB	100 ± 15 Ohm	101 ± 6 Ohm
62.5 MHz	17.0 dB/100m	38.4 dB	35.4 dB	22 dB	19 dB	27.8 dB	24.8 dB	23.5 dB	21.5 dB	100 ± 15 Ohm	101 ± 6 Ohm
100 MHz	22.0 dB/100m	35.3 dB	32.3 dB	14 dB	11 dB	23.8 dB	20.8 dB	22.5 dB	20.1 dB	100 ± 15 Ohm	

## Current

### Max. Recommended Current [A]

15 pF/ft

## Temperature Range

UL Temp Rating:	75°C
Storage Temperature Range:	-40°C to +85°C
Operating Temperature Range:	-40°C To +75°C

## Mechanical Characteristics

Bulk Cable Weight:	150 lbs/1000ft
Max. Pull Tension:	100 lbs

## Standards

NEC Articles:	Article 800
NEC/(UL) Compliance:	CM
CEC/C(UL) Compliance:	CMG, HL
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
CPR Euroclass:	Fca
Data Category:	Category 5e
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 5e

## Applicable Environmental and Other Programs

Environmental Space:	Outdoor
----------------------	---------

## Suitability

Suitability - Aerial:	No
Suitability - Burial:	Yes - Telcordia, IEC, ICEA
Suitability - Indoor:	No
Suitability - Non-Halogenated:	Yes
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

## Product Notes

Notes:	Operating temperatures are subject to length de-rating
--------	--

## History

Update and Revision:	Revision Number: 0.40 Revision Date: 04-29-2024
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.