



Part Number: 1304A

CatSnake, Tactical CAT5E, #24-4pr, Bonded-Pairs

Product Description

CatSnake® Tactical CAT5E, 4-24 AWG bonded-pairs, stranded bare copper conductors, polyolefin insulation, PVC jacket with sequential marking at two foot intervals

Technical Specifications

Product Overview

Suitable Applications:	Field Deployable Cat 5e Patch, CobraNet, eSnake, Ethersound, Digital Audio Over Ethernet, POE, POE+
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
24	7x32	BC - Bare Copper	0.024 in	4

Conductor Count:	8
Total Number of Pairs:	4

Insulation

Material	Nominal Diameter
PO - Polyolefin	0.041 in

Bonded-Pair:	N/A
--------------	-----

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.250 in

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance	Nominal Conductor DCR
25 Ohm/1000ft	3 %	25 Ohm/1000ft

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
66 pF/ft	15 pF/ft

Delay

Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]	Typical Delay Skew
510 ns/100m	25 ns/100m	70 %	15 ns/ft

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2.0 dB/100m	65.3 dB	65.3 dB	63.3 dB	62.9 dB	63.8 dB	60.8 dB	20.0 dB	100 +/- 12	105 +/- 10
4 MHz	4.1 dB/100m	56.3 dB	56.3 dB	52.2 dB	51.5 dB	51.8 dB	48.8 dB	23.0 dB	100 +/- 12	100 +/- 10
8 MHz	5.8 dB/100m	51.8 dB	51.8 dB	46.0 dB	45.0 dB	45.7 dB	42.7 dB	24.5 dB	100 +/- 12	100 +/- 10
10 MHz	6.5 dB/100m	50.3 dB	50.3 dB	43.8 dB	42.6 dB	43.8 dB	40.8 dB	25.0 dB	100 +/- 12	100 +/- 10
16 MHz	8.2 dB/100m	47.2 dB	47.2 dB	39.0 dB	37.5 dB	39.7 dB	36.7 dB	25.0 dB	100 +/- 12	100 +/- 10
20 MHz	9.3 dB/100m	45.8 dB	45.8 dB	36.5 dB	34.8 dB	37.8 dB	34.8 dB	25.0 dB	100 +/- 12	100 +/- 10
25 MHz	10.4 dB/100m	44.3 dB	44.3 dB	33.9 dB	31.9 dB	35.8 dB	32.8 dB	24.3 dB	100 +/- 15	100 +/- 10
31.25 MHz	11.7 dB/100m	42.9 dB	41.9 dB	31.2 dB	29.0 dB	33.9 dB	30.9 dB	23.6 dB	100 +/- 15	100 +/- 10
62.5 MHz	17.0 dB/100m	38.4 dB	38.4 dB	21.4 dB	18.3 dB	27.9 dB	24.9 dB	21.5 dB	100 +/- 15	100 +/- 10
100 MHz	22.0 dB/100m	35.3 dB	35.3 dB	13.3 dB	9.2 dB	23.8 dB	20.8 dB	20.1 dB	100 +/- 18	100 +/- 10
155 MHz	28.1 dB/100m	32.4 dB	32.4 dB	4.4 dB	0.0 dB	20.0 dB	17.0 dB	18.8 dB	100 +/- 18	100 +/- 10
200 MHz	32.4 dB/100m	30.8 dB	30.8 dB		9.2 dB	17.8 dB	14.8 dB	18.0 dB	100 +/- 18	100 +/- 10
250 MHz	44.2 dB/100m	29.3 dB	29.3 dB		0 dB	15.8 dB	12.8 dB	17.3 dB	100 +/- 18	100 +/- 10
310 MHz	50.1 dB/100m	27.9 dB	27.9 dB			14.0 dB	11.0 dB	16.7 dB	100 +/- 18	100 +/- 10
350 MHz	53.8 dB/100m	27.1 dB	27.1 dB			12.9 dB	9.9 dB	16.3 dB	100 +/- 18	100 +/- 10
300 MHz	48.6 dB/100m	28.2 dB	28.2 dB			12.9 dB	9.9 dB	18 dB	100 ± 22 Ohm	100 ± 10 Ohm
310 MHz	49.5 dB/100m	27.9 dB	27.9 dB					18 dB		
350 MHz	53.2 dB/100m	27.2 dB	27.2 dB					17 dB		

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Installation Temp Range:	-0 To 60C
Non-UL Temp Rating:	+75°C
Storage Temp Range:	-30°C To +75°C
Operating Temp Range:	-30°C To +75°C

Mechanical Characteristics

Cold Bend Test:	-30°C Compliance per UL 1581
Bulk Cable Weight:	26 lbs
Max Recommended Pulling Tension:	40 lbs
Min Bend Radius During Installation:	2.5 in
Min Bend Radius/Minor Axis:	1.0 in

Standards

NEC/(UL) Specification:	N/A
ISO/IEC Compliance:	11801 Category 5e Patch
Data Category:	Category 5e
ANSI Compliance:	S-90-661-2012 Category 5e Patch, ANSI/NEMA WC-63.1 Category 5e Patch
Telecommunications Standards:	TIA/EIA-568-B.2
IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3
Other Specification:	NEMA WC-63.1 Category 5, ICEA 661, Category 5e Patch, TIA/EI-568-B.2, Category 5e
Other Standards:	NEMA WC-63.1 Category 5e Patch, ANSI/ICEA 661 Individually Unshielded Twisted Pair Indoor Cable

Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No

EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2006-02-20
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	No

Flammability, LS0H, Toxicity Testing

ISO/IEC Flammability:	60332-1
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	N
---------------	---

Part Number

Variants

Item #	Color	UPC	Length
1304A B591000	Black, Matte	612825111108	1,000 ft
1304A B59500	Black, Matte	612825111115	500 ft

Patent:	https://www.belden.com/resources/patents
---------	---

Product Notes

Notes:	EtherNet/IP is a Trademark of ControlNet Internation, Ltd. Under License by Open DeviceNet Vendor Association, Inc. Operating Temperatures Are Subject to Length De-rating.
--------	---

History

Update and Revision:	Revision Number: 0.321 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.