




Product: [1319SB](#) 

Category 6 Shipboard Cable, ABS, 4 Pair, LSZH

Product Description

Category 6 Shipboard Cable, ABS, 4 Pair, 23 AWG Solid Bare Copper Conductors, CMG-LS, Upjacketed, LSZH Jacket

Technical Drawing



Technical Specifications

Product Overview

Suitable Applications:	Shipboard, Premise Horizontal Cable, Ethernet 1000BASE-T, Ethernet 100BASE-TX, Ethernet 10BASE-T, PoE++, PoE+, PoE
------------------------	--

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
23 AWG	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
PO - Polyolefin	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Inner Jacket

Material	Nom. Diameter	Ripcord
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.239 in (6.07 mm)	Yes

Outer Shield

Shield Type	Material	Coverage
Tape	Nomex®	100%

Outer Jacket

Separator	Material	Material Trade Name	Nom. Diameter	Ripcord
Dielectric Tape (Patented)	LSZH - Low Smoke Zero Halogen (Flame Retardant)	Haloarrest®	0.293 in (7.44 mm)	No

Overall Cable Diameter (Nominal): 0.293 in (7.44 mm)

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
93.8 Ohm/km (28.6 Ohm/1000ft)	160 pF/100m

Delay

Frequency	Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
100 MHz	537.6 ns/100m	45 ns/100m	70%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted) [Ohm]	Max./Min. Fitted Impedance [Ohm]	Min. TCL [dB]	Min. ELTCL [dB]
1	2.0 dB/100m	74.3	72.3	70.3	67.8	64.8	20.0	100 ± 15	100 ± 15	40.0	35.0
4	3.8 dB/100m	65.3	63.3	59.5	55.7	52.7	23.0	100 ± 15	100 ± 15	40.0	23.0
8	5.3 dB/100m	60.8	58.8	53.4	49.7	46.7	24.5	100 ± 15	100 ± 15	40.0	16.9
10	6.0 dB/100m	59.3	57.3	51.4	47.8	44.8	25.0	100 ± 15	100 ± 15	40.0	15.0
16	7.6 dB/100m	56.3	54.3	46.7	43.7	40.7	25.0	100 ± 15	100 ± 15	38.0	10.9
20	8.5 dB/100m	54.8	52.8	44.3	41.7	38.7	25.0	100 ± 15	100 ± 15	37.0	9.0
25	9.5 dB/100m	53.3	51.3	41.8	39.8	36.8	24.3	100 ± 15	100 ± 15	36.0	7.0
31.25	10.7 dB/100m	51.9	49.9	39.2	37.9	34.9	23.6	100 ± 15	100 ± 15	35.1	5.1
62.5	15.4 dB/100m	47.4	45.4	30.0	31.8	28.8	21.5	100 ± 15	100 ± 15	32.0	
100	19.8 dB/100m	44.3	42.3	22.5	27.8	24.8	20.1	100 ± 15	100 ± 15	30.0	
155	25.2 dB/100m	41.5	39.5	14.3	23.9	20.9	18.8	100 ± 22	100 ± 15	28.1	
200	29.0 dB/100m	39.8	37.8	8.8	21.7	18.7	18.0	100 ± 22	100 ± 15	27.0	
250	32.8 dB/100m	38.3	36.3	3.5	19.8	16.8	17.3	100 ± 32	100 ± 15	26.0	

Voltage

UL Voltage Rating
300 V (CMG-LS)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
105°C	-20°C To +75°C	0°C To +50°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1.25 in (31.8 mm)	3.0 in (76 mm)

Max. Pull Tension: 25 lbs (11 kg)

Bulk Cable Weight: 42 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Non-Halogenated, Aerial - When supported by messenger wire
Flammability / Reaction to Fire:	UL 1685 (UL Loading-Limited Smoke), IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CMG-LS
CEC / C(UL) Compliance:	CMG-ST1
ICEA Compliance:	S-116-732, S-56-434, S-99-689, S-100-685
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6

TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6
Marine Compliance:	ABS certificate 18-HS1803790-PDA
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Print Includes Descending Footage Markings from Max. Put-Up Length to 0.
--------	---

History

Update and Revision:	Revision Number: 0.549 Revision Date: 01-20-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1319SB 0101000	Black	Reel	1,000 ft	612825111825	C
1319SB 0105000	Black	Reel	5,000 ft	612825111832	

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.