


**Product:** [1279P](#) 



RGB Video, Mini Hi-Res, 5 Coax 25 AWG TC, Plenum

## Product Description

RGB Video Coax, 5 Coax 25 AWG solid tinned copper conductors, foam FEP insulation, Duobond® foil + 95% tinned copper interlocked serve shield, inner PVC jackets, Plenum, PVC jacket.

## Technical Specifications

### Product Overview

Suitable Applications:	RGB Projectors, LCD Projectors, Video Distribution, Component Video, Graphic Displays, Special Effects Editing, Animation, Video Post Production, Home Theater, Offices, Boardrooms, Auditoriums, Teleconferencing, Theaters
------------------------	--

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
25	Solid	TC - Tinned Copper	0.018 in	5

Conductor Count:	5
------------------	---

#### Insulation

Material	Nominal Diameter
FEP - Fluorinated Ethylene Propylene (Foam)	0.074 in

#### Inner Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duobond®	100%
French Braid	2	Tinned Copper (TC)		95%

Table Notes:	Tape lightly bonded to dielectric
--------------	-----------------------------------

#### Inner Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.111 in

#### Outer Shield Material

Material
Tri-Laminate (Alum+Poly+Alum)

#### Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.33 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Inner Shield DCR	Outer Conductor DCR
34 Ohm/1000ft	5.4 Ohm/1000ft	5.4 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Shield

16.8 pF/ft

#### Inductance

##### Nominal Inductance

0.087  $\mu$ H/ft

#### Impedance

##### Nominal Characteristic Impedance

75 Ohm

#### Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5 - 850 MHz	20 dB

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.5 dB/100ft
5 MHz	1.2 dB/100ft
50 MHz	3.8 dB/100ft
100 MHz	5.2 dB/100ft
200 MHz	7.1 dB/100ft
400 MHz	10 dB/100ft
750 MHz	14.3 dB/100ft
1000 MHz	16.9 dB/100ft
2250 MHz	25.5 dB/100ft
3000 MHz	33.9 dB/100ft

#### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.26 ns/ft	81%

#### Voltage

##### UL Voltage Rating

300 V RMS

### Temperature Range

Non-UL Temp Rating:	75°C
UL Temp Rating:	60°C
Operating Temp Range:	-20°C To +75°C

### Mechanical Characteristics

Bulk Cable Weight:	60 lbs/1000ft
Max. Pull Tension:	83 lbs
Min Bend Radius (Overall):	3.25 in
Min Bend Radius (Each Coax):	1.1 in

### Standards

NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP
RG Type:	Sub-miniature 59

### Applicable Environmental and Other Programs

Environmental Space:	Indoor - Plenum
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No

EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Indoor:	Yes
-----------------------	-----

## Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262
CSA Flammability:	FT6
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

## Part Number

Non-Plenum Number:	1279R
--------------------	-------

## Variants

Item #	Color	Putup Type	Length	UPC
1279P 010250	Black	Reel	250 ft	612825110279
1279P 010500	Black	Reel	500 ft	612825110286
1279P 0101000	Black	Reel	1,000 ft	612825110262
1279P 008250	Gray	Reel	250 ft	612825110248
1279P 008500	Gray	Reel	500 ft	612825110255
1279P 0081000	Gray	Reel	1,000 ft	612825110231

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## History

Update and Revision:	Revision Number: 0.334 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.