




Product: [1285B](#) 

RW90 600V, 4 Str BC, XLPE Ins, PVC Jkt, 90C Dry/Wet CSA HL SUN RES

Product Description

RW90 600V, 4 AWG Bare Copper, XLPE Insulation, PVC Outer Jacket, 90C Dry/Wet CSA HL SUN RES

Technical Specifications

Product Overview

Suitable Applications:	CEC Power and Control Applications
------------------------	------------------------------------

Construction Details

Conductor

Element	No. of Elements	Stranding	Material
Conductor(s)	1	7x12	BC - Bare Copper

Insulation

Material	Nom. Thickness	Color Code
XLP, XLPO, XLPE (Thermoset)	0.060 in	black

Outer Jacket

Material
PVC - Polyvinyl Chloride

Overall Cable Diameter (Nominal):	3.2 in (81 mm)
-----------------------------------	----------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR
Conductor(s)	0.26 Ohm/1000ft (0.85 Ohm/km)

Voltage

UL Voltage Rating	Voltage Rating
600 V RMS	600V RMS (600V)

Mechanical Characteristics

Temperature

Operating	Installation
-40°C To +90°C	-25°C To +90

Bulk Cable Weight:	471 lbs/1000ft (701 kg/km)
--------------------	----------------------------

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, UV Resistance, Burial
CEC / C(UL) Compliance:	RW90, C22.2 #230, #38
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.14 Revision Date: 03-05-2026
----------------------	---

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.