



Product: [1338A](#)

Fieldbus, 2 Pr #18 Str TC, PO Ins, IS/OS, PVC Jkt, 600V TC-ER

[Request Sample](#)

Product Description

Fieldbus, 2 Pair 18AWG (7x26) Tinned Copper, PO Insulation, Individual & Overall Beldfoil® Shield, Orange PVC Outer Jacket, 600V TC-ER

Technical Specifications

Product Overview

Suitable Applications:	harsh environment digital and serial two-way communication, oil and gas extraction and refining sites, petrochemical, Profibus process automation or Foundation FieldBus process automation, extreme temperature environments, exposure to humidity/moisture, dust, and oil, remote locations long distance applications, etc.
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors	No. of Pairs
18	7x26	TC - Tinned Copper		2
18		TC - Tinned Copper	1	

Conductor Count:	5
------------------	---

Insulation

Material
PVC - Polyvinyl Chloride
PP - Polypropylene

Color Chart

Number	Color
1	Blue, Orange and Numbered
2	
3	

Color Chart 2

Color
Green/Yellow

Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	18	7x26
	Tinned Copper (TC)				

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	20	7x28

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.51 in

Electrical Characteristics

Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR
7.5 Ohm/1000ft	5.86 Ohm/1000ft

Capacitance

Max. Capacitance Unbalance	Nom. Capacitance Conductor to Other Conductor to Shield	Nom. Mutual Capacitance
1.2 pF/ft	45 pF/ft	24 pF/ft

Inductance

Nominal Inductance
0.22 μ H/ft

Impedance

Nominal Characteristic Impedance
100 Ohm

High Frequency (Nominal/Typical)

Nom. Insertion Loss
0.08 dB/100ft

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Max./Min. Input Impedance (unFitted)
0.031 MHz	0.091 dB/100ft	100 Ohm

Current

Element	Max. Recommended Current [A]
Per Conductor	5.2 Amps per Conductor

Voltage

UL Voltage Rating
600 V RMS

Electrical Characteristics Notes: Max. Propagation Delay Change From 7.812 kHz to 39.06 kHz: 518 pS/ft

Other Electrical Characteristic 2: 31.25 KBits/sec

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-30°C to +75°C

Mechanical Characteristics

Max. Pull Tension:	112 lbs
Min. Bend Radius/Minor Axis:	5.1 in

Standards

NEC Articles:	Article 336
NEC/(UL) Compliance:	TC-ER

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Oil Resistance:	Yes

Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
UL voltage rating:	600 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
1338A 0037500	Orange	Reel	7,500 ft	612825112273

History

Update and Revision:	Revision Number: 0.349 Revision Date: 05-26-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.