



Product: [1345F](#)

Fieldbus, 2 C #15+18 Str TC, PVC-NYL&FEP Ins, IS+OA TC Brd, TPE Jkt, High Flex

[Request Sample](#)

Product Description

Fieldbus, 2 Conductor 15+18AWG (65x33+65x36) Tinned Copper, PVC-NYL&FEP Insulation, Individual Beldfoil® & OA Tinned Copper Braid(65%) Shield, Orange TPE Outer Jacket, High Flex

Technical Specifications

Product Overview

Suitable Applications:	harsh environment digital and serial two-way communication, oil and gas extraction and refining sites, petrochemical, Profibus process automation or Foundation FieldBus process automation, extreme temperature environments, exposure to humidity/moisture, dust, and oil, remote locations long distance applications, etc.
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
15	65x33	TC - Tinned Copper	1
18		TC - Tinned Copper	1

Conductor Count:	4
------------------	---

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.021 in
PE - Polyethylene (Foam)	0.053 in

Color Chart

Number	Color
1 (15 AWG)	Red & Black
2 (18 AWG)	Blue & White

Inner Shield Material

Type	Layer	Material	Coverage [%]
Tape	15 AWG Pair	Bi-Laminate (Alum+Poly)	100%

Outer Shield Material

Type	Material	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Braid	Tinned Copper (TC)	65%	TC - Tinned Copper	18	65x36

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
TPE - Thermoplastic Elastomer	0.480 in	0.060 in

Electrical Characteristics

Conductor DCR

Element	Nominal Conductor DCR	Nominal Outer Shield DCR
15 AWG	3.6 Ohm/1000ft	1.8 Ohm/1000ft
	6.9 Ohm/1000ft	

Capacitance

Element	Nom. Capacitance Conductor to Conductor
18 AWG Pair Only	
	12.0 pF/ft

Inductance

Element	Nominal Inductance
15 AWG Pair Only	0.174 µH/ft

Impedance

Nominal Characteristic Impedance
100 Ohm
120 Ohm

Delay

Max. Delay	Max. Delay Description	Nominal Delay	Nominal Velocity of Propagation (VP) Description
1.36 ns/ft	18 AWG Pair Only		18 AWG Pair Only
		1.36 ns/ft	

High Freq

Element	Frequency [MHz]	Max./Min. Input Impedance (unFitted)
18 AWG Pair Only	0.125 MHz	120 Ohm
	0.5 MHz	
	1 MHz	

Current

Element	Max. Recommended Current [A]
15 AWG	8 Amps per Conductor
18 AWG	5 Amps per Conductor

Voltage

UL Description	UL Voltage Rating
CMG, PLTC-ER	300 V
UL AWM 20201	600 V

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-30°C to +75°C

Mechanical Characteristics

Oil Resistance:	Yes
Bulk Cable Weight:	133 lbs/1000ft
Max. Pull Tension:	205 lbs
Min Bend Radius/Minor Axis:	4.6 in

Standards

NEC Articles:	Article 725, Article 800
NEC/(UL) Compliance:	CMG, PLTC-ER
CEC/C(UL) Compliance:	CMG
UL AWM Style Compliance:	20201
CSA AWM Compliance:	AWM I/II A
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)

EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Oil Resistance:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4
IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
1345F T5U1000	Gray T5U	Reel	1,000 ft	612825112327

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	High-Flex. Thick. Meter marks on jacket to aid users in installation. ODVA DeviceNet is an Open DeviceNet Vendor Association, Inc. trademark. Jacket printed ""1PR16"" instead of ""1PR15"" due to UL requirements for CMG Listing.
--------	---

History

Update and Revision:	Revision Number: 0.375 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.