



Part Number: 1348A

CC Link, 3 C #20 Str BC, PO Ins, OS+TC Brd, PVC Jkt, CM

[Request Sample](#)

Product Description

CC Link, 3 Conductor 20AWG (7x28) Bare Copper, PO Insulation, Overall Beldfoil®+Tinned Copper Braid(78%) Shield, PVC Outer Jacket, CM

Technical Specifications

Product Overview

Suitable Applications:	CC Link
------------------------	---------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
20	7x28	BC - Bare Copper	3

Conductor Count:	3
------------------	---

Insulation

Material	Nominal Wall Thickness
FHDPE - Foamed High Density Polyethylene	0.028 in

Color Chart

Number	Color
1	Blue
2	Yellow
3	White

Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	1	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	22	19x34 mm
Braid	2	TC - Tinned Copper		78 %			

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.303 in	0.035 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
9.5 Ohm/1000ft	8 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
18.3 pF/ft

Impedance

Nominal Characteristic Impedance
120 Ohm

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-30°C To +60°C

Mechanical Characteristics

Bulk Cable Weight:	49 lbs/1000ft
Max Recommended Pulling Tension:	46 lbs
Min Bend Radius/Minor Axis:	3 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
Other Specification:	Mitsubishi CC Link Signal

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-08-15
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length	Footnote
1348A 0021000	Red	612825112365	1,000 ft	C
1348A 0025000	Red	612825112372	5,000 ft	C Z

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

History

Update and Revision:	Revision Number: 0.296 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.