



Product: [1366A](#)

Fieldbus, 20 Pr #16 Str TC, PO Ins, IS/OS, PVC Jkt, CMG

Request Sample

Product Description

Fieldbus, 20 Pair 16AWG (7x24H) Tinned Copper, PO Insulation, Individual & Overall Beldfoil® Shield, Orange PVC Outer Jacket, CMG

Technical Specifications

Product Overview

Suitable Applications:	harsh environment digital and serial two-way communication, oil and gas extraction and refining sites, petrochemical, Profibus process automation or Foundation FieldBus process automation, extreme temperature environments, exposure to humidity/moisture, dust, and oil, remote locations long distance applications, etc.
------------------------	--

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Pairs
Pair(s)	16	7x24	TC - Tinned Copper	20

Conductor Count:	40
------------------	----

Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	0.029 in

Color Chart

Number	Color
1	Blue, Orange and Numbered
2	
3	
4	
5	
6	
7	
8	
9	
10	
11	
12	
13	
14	
15	
16	
17	
18	
19	
20	

Inner Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	20	7x28

Outer Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	16	7x24

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	1.393 in	0.085 in	Yes

Construction and Dimensions

Stranding

Twists
5 twist/ft

Electrical Characteristics

Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Outer Shield DCR
7.5 Ohm/1000ft	4.2 Ohm/1000ft	4.9 Ohm/1000ft

Capacitance

Max. Capacitance Unbalance	Nom. Capacitance Conductor to Shield	Nom.Mutual Capacitance
1.2 pF/ft	45 pF/ft	24 pF/ft

Inductance

Nominal Inductance
0.19 µH/ft

Impedance

Nominal Characteristic Impedance
100 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
0.039 MHz	0.08 dB/100ft

Delay

Nominal Velocity of Propagation (VP) [%]
66%

High Frequency

Max. Insertion Loss (Attenuation)	Max./Min. Input Impedance (unFitted)
0.091 dB/100ft	100 Ohm

Current

Element	Max. Recommended Current [A]
Per Conductor	5.2 Amps per Conductor

Voltage

UL Voltage Rating
300 V RMS

Electrical Characteristics Notes: Max Propagation Delay Change From 7.812 kHz to 39.06 kHz: 518 pS/ft

Other Electrical Characteristic 2: 31.25 KBits/sec

Temperature Range

UL Temp Rating:	105°C
Operating Temperature Range:	-40°C to +105°C

Mechanical Characteristics

Oil Resistance:	Yes
Bulk Cable Weight:	810 lbs/1000ft
Max. Pull Tension:	1428 lbs
Min. Bend Radius/Minor Axis:	13.9 in

Standards

NEC Articles:	Article 725, Article 727, Article 800
NEC/(UL) Compliance:	CMG, ITC-ER, PLTC-ER
CEC/C(UL) Compliance:	CMG

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

CSA/C(UL) Flammability:	FT4
UL Flammability:	UL1685 FT4 Loading
IEC Flammability:	IEC 60332-3-24
IEEE Flammability:	1202
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
1366A 0031000	Orange	Reel	1,000 ft	612825112709

History

Update and Revision:	Revision Number: 0.249 Revision Date: 12-22-2023
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.