


**Product:** [1398S5](#) 

RGB Video, Banana Peel 5 25 AWG Coax, CMP



### Product Description

Mini-Hi Res RGB Video Cable , 5 25 AWG solid tinned copper coax, foam FEP insulation, Beldfoil®; 95% tinned copper serve, inner Flamarrest® jackets, CMP rated.

### Technical Specifications

#### Product Overview

Suitable Applications:	Video
------------------------	-------

#### Physical Characteristics (Overall)

##### Conductor

AWG	Material	Nominal Diameter	No. of Coax
25	TC - Tinned Copper	0.018 in	5

Conductor Count:	5
------------------	---

##### Insulation

Material	Nominal Diameter
FEP - Fluorinated Ethylene Propylene (Foam)	0.074 in

Table Notes:	Gas Injected
--------------	--------------

##### Color Chart 3

Number	Color
1	Gray #1
2	Gray #2
3	Gray #3
4	Gray #4
5	Gray #5

##### Inner Shield

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Spiral Serve / Screen	2	Tinned Copper (TC)		95%

##### Inner Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.105 in

##### Outer Jacket

Material	Nominal Diameter
Banana Peel (No Overall Jacket)	0.275 in

#### Construction and Dimensions

##### Cabling

Filler
--------

Bonded Spline

## Electrical Characteristics

### Conductor DCR

Nominal Conductor DCR	Nominal Inner Shield DCR	Outer Conductor DCR
34 Ohm/1000ft	5.4 Ohm/1000ft	5.4 Ohm/1000ft

### Capacitance

Nom. Capacitance Conductor to Shield
17 pF/ft

### Impedance

Nominal Characteristic Impedance
75 Ohm

### Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5-1000 MHz	15 dB

### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.52 dB/100ft
5 MHz	1.17 dB/100ft
50 MHz	3.7 dB/100ft
100 MHz	4.9 dB/100ft
200 MHz	6.7 dB/100ft
400 MHz	9.5 dB/100ft
750 MHz	13.4 dB/100ft
900 MHz	15 dB/100ft
1000 MHz	15.8 dB/100ft
3000 MHz	31.2 dB/100ft

### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.27 ns/ft	80%

### Voltage

UL Voltage Rating
300 V RMS

## Temperature Range

Operating Temp Range:	0°C To +60°C
-----------------------	--------------

## Mechanical Characteristics

Bulk Cable Weight:	40 lbs/1000ft
Max. Pull Tension:	20 lbs
Min Bend Radius (Overall):	2.8 in
Min Bend Radius (Each Coax):	1.1 in

## Standards

NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP
RG Type:	Sub-miniature 59

## Applicable Environmental and Other Programs

Environmental Space:	Indoor - Plenum
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes

EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
MII Order #39 (China RoHS):	Yes

### Suitability

Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes

### Flammability, LSOH, Toxicity Testing

UL Flammability:	NFPA 262
UL voltage rating:	300 V RMS

### Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

### Related Part Numbers

Non-Plenum Number:	1397S5
--------------------	--------

### Variants

Item #	Color	Put-Up Type	Length	UPC
1398S5 008250	Gray	Reel	250 ft	612825114567
1398S5 008500	Gray	Reel	500 ft	612825114574
1398S5 0081000	Gray	Reel	1,000 ft	612825114550

### Product Notes

Notes:	BananaPeel®, each coax numbered
--------	---------------------------------

### History

Update and Revision:	Revision Number: 0.172 Revision Date: 12-15-2021
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.