



**Product:** [1306SB](#)

Composite Shipboard, 18 AWG Coax Video, 1 PR 18 AWG Power

### Product Description

Composite Shipboard, 18 AWG Coax BC, BC Braid Shield 95% coverage, FPE insulation for video and 1 PR 18 AWG BC, stranded (7x26), PP insulation for power, overall CMG-LS rating, LSZH jacket.

### Technical Specifications

#### Product Overview

Suitable Applications:	Surveillance, CCTV Camera, PTZ (Pan-Tilt-Zoom), Shipboard, Low Smoke
------------------------	--

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Conductors	No. of Coax
18	Solid	BC - Bare Copper	0.04 in		1
18	7x26	BC - Bare Copper	0.046 in	2	

Conductor Count:	3
------------------	---

##### Insulation

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.18 in
PP - Polypropylene	0.058 in

##### Color Chart

Number	Color
1	Black and Red

##### Inner Shield

Type	Material	Coverage [%]
Braid	Bare Copper (BC)	95%

##### Outer Shield

Type	Layer	Material	Coverage [%]
Braid	1	Bare Copper (BC)	95%

##### Outer Jacket

Material	Nominal Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.275x0.514 in

#### Electrical Characteristics

##### Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Inner Shield DCR	Outer Conductor DCR
6.4 Ohm/1000ft	6.4 Ohm/1000ft		3.1 Ohm/1000ft	3.1 Ohm/1000ft
6.4 Ohm/1000ft				

##### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
24 pF/ft	16.3 pF/ft

Operating Voltage:	300 V RMS
--------------------	-----------

**Inductance**

Nominal Inductance
0.097 $\mu$ H/ft

**Impedance**

Nominal Characteristic Impedance
75 Ohm

**High Frequency (Nominal/Typical)**

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.2 dB/100ft
5 MHz	0.45 dB/100ft
10 MHz	0.64 dB/100ft
50 MHz	1.46 dB/100ft
100 MHz	2.1 dB/100ft
200 MHz	3.0 dB/100ft
400 MHz	4.3 dB/100ft
700 MHz	5.8 dB/100ft
900 MHz	6.7 dB/100ft
1000 MHz	7.1 dB/100ft

**Delay**

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.24 ns/ft	82%

**Voltage**

UL Voltage Rating
300 V RMS

**Temperature Range**

Operating Temperature Range:	-30°C To +75°C
------------------------------	----------------

**Mechanical Characteristics**

Bulk Cable Weight:	67 lbs/1000ft
Max. Pull Tension:	114 lbs
Min. Bend Radius/Minor Axis:	2.75 in

**Standards**

NEC Articles:	Article 800
NEC/(UL) Compliance:	CMG-ST1
CEC/C(UL) Compliance:	CMG-ST1
CPR Euroclass:	Fca
IEEE Compliance:	Std. 45 Clause 23
RG Type:	6

**Applicable Environmental and Other Programs**

Environmental Space:	Outdoor - Aerial
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

**Suitability**

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only
Suitability - Sunlight Resistance:	No

## Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading, Limited Smoke
CSA Flammability:	FT4
IEC Flammability:	IEC 60332-1-2, IEC 60332-3-22
IEEE Flammability:	IEEE 1202
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Related Part Numbers

### Variants

Item #	Color	Put-Up Type	Length	UPC
1306SB 010500	Black	Reel	500 ft	612825111238
1306SB 0101000	Black	Reel	1,000 ft	612825111221

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## Product Notes

Notes:	Coax jacket diameter: .275 in, Pair jacket diameter: .204 in
--------	--

## History

Update and Revision:	Revision Number: 0.309 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.