



REPRESENTATIVE IMAGE

Product: [1314SB](#)

Speaker Cable, 2 C #14 Str TC, LSZH Jacket, CMG-LS, ABS Certified, Flexible

Product Description

Speaker Cable, 2 Conductor 14 AWG (41 x 30) Tinned Copper, PP insulation, LSZH jacket, Ripcord, CMG-LS-rated, Shipboard ABS Type Approved, Flexible

Technical Specifications

Product Overview

Suitable Applications:	Shipboard and offshore environments, Speaker; Low voltage analog signals and control
------------------------	--------------------------------------------------------------------------------------

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	2	14 AWG	41x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PP - Polypropylene	0.011 in (0.28 mm)	0.095 in (2.4 mm)	Black, White

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.052 in (1.3 mm)	0.294 in (7.47 mm)	Yes

Overall Cable Diameter (Nominal):	0.294 in (7.47 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	2.42 Ohm/1000ft (7.94 Ohm/km)	29 pF/ft (95 pF/m)	22 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V (CMG-LS)

Mechanical Characteristics

Temperature

UL Temperature	Operating
105°C	-20°C to +105°C

Bend Radius

Stationary Min.	Installation Min.
2.9 in (74 mm)	2.9 in (74 mm)

Max. Pull Tension:	109.2 lbs (49.53 kg)
Bulk Cable Weight:	53 lbs/1000ft (79 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance
----------------------------	------------------------------------------------------

Flammability / Reaction to Fire:	UL1685 FT4 Loading, Limited Smoke, IEEE 1202 FT4, 60332-1, 60332-3-22 (Category A)
CPR Compliance:	CPR Euroclass: Dca-s1,d1,a1
NEC / UL Compliance:	Article 800, CMG-LS
CEC / C(UL) Compliance:	CMG-ST1
IEEE Compliance:	Std. 45 clause 23
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	ABS Type Approval Certificate 06-HS184641E

History

Update and Revision:	Revision Number: 0.308 Revision Date: 04-08-2022
----------------------	--------------------------------------------------

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
1314SB 0101000	Black	Reel	1,000 ft	612825111771

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.