




Product: [1319SB](#) 

Category 6 Shipboard Cable, ABS, 4 Pair, LSZH

Product Description

Category 6 Shipboard Cable, ABS, 4 Pair, 23 AWG Solid Bare Copper Conductors, CMG-LS, Upjacketed, LSZH Jacket

Technical Drawing



Technical Specifications

Product Overview

Suitable Applications:	Shipboard, Premise Horizontal Cable, Ethernet 1000BASE-T, Ethernet 100BASE-TX, Ethernet 10BASE-T, PoE++, PoE+, PoE
------------------------	--

Construction Details

Conductor

AWG	Stranding	Material	Number of Pairs
23	Solid	BC - Bare Copper	4

Insulation

Material	Nom. Insulation Diameter	Color Code
PO - Polyolefin	0.041	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Bonded-Pair:	No
--------------	----

Inner Jacket Material

Material	Nom. Diameter	Ripcord
PE - Polyethylene	0.239 in	Yes

Outer Shield Material

Type	Material	Coverage
Tape	Nomex®	100%

Outer Jacket Material

Separator Material	Material	Material Trade Name	Nom. Diameter	Ripcord
Dielectric Tape (Patented)	LSZH - Low Smoke Zero Halogen (Flame Retardant)	Haloarrest®	0.293 in	No

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. DCR Unbalance	Max. Capacitance Unbalance	Nom. Mutual Capacitance
93.8 Ohm/km	3%	160 pF/100m	15 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nom. Velocity of Propagation (VP) [%]
100 MHz	537.6 ns/100m	45 ns/100m	70%

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.0 dB/100m	74.3 dB	72.3 dB	70.3 dB	67.8 dB	64.8 dB	20.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	35.0 dB
4 MHz	3.8 dB/100m	65.3 dB	63.3 dB	59.5 dB	55.7 dB	52.7 dB	23.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	23.0 dB
8 MHz	5.3 dB/100m	60.8 dB	58.8 dB	53.4 dB	49.7 dB	46.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	16.9 dB
10 MHz	6.0 dB/100m	59.3 dB	57.3 dB	51.4 dB	47.8 dB	44.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	15.0 dB
16 MHz	7.6 dB/100m	56.3 dB	54.3 dB	46.7 dB	43.7 dB	40.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	38.0 dB	10.9 dB
20 MHz	8.5 dB/100m	54.8 dB	52.8 dB	44.3 dB	41.7 dB	38.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	37.0 dB	9.0 dB
25 MHz	9.5 dB/100m	53.3 dB	51.3 dB	41.8 dB	39.8 dB	36.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 15 Ohm	36.0 dB	7.0 dB
31.25 MHz	10.7 dB/100m	51.9 dB	49.9 dB	39.2 dB	37.9 dB	34.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 15 Ohm	35.1 dB	5.1 dB
62.5 MHz	15.4 dB/100m	47.4 dB	45.4 dB	30.0 dB	31.8 dB	28.8 dB	21.5 dB	100 ± 15 Ohm	100 ± 15 Ohm	32.0 dB	
100 MHz	19.8 dB/100m	44.3 dB	42.3 dB	22.5 dB	27.8 dB	24.8 dB	20.1 dB	100 ± 15 Ohm	100 ± 15 Ohm	30.0 dB	
155 MHz	25.2 dB/100m	41.5 dB	39.5 dB	14.3 dB	23.9 dB	20.9 dB	18.8 dB	100 ± 22 Ohm	100 ± 15 Ohm	28.1 dB	
200 MHz	29.0 dB/100m	39.8 dB	37.8 dB	8.8 dB	21.7 dB	18.7 dB	18.0 dB	100 ± 22 Ohm	100 ± 15 Ohm	27.0 dB	
250 MHz	32.8 dB/100m	38.3 dB	36.3 dB	3.5 dB	19.8 dB	16.8 dB	17.3 dB	100 ± 32 Ohm	100 ± 15 Ohm	26.0 dB	

Voltage

UL Voltage Rating
300 V (CMG-LS)

Mechanical Characteristics

Temperature

UL Rating	Operating	Installation	Storage
105°C	-20°C To +75°C	0°C To +50°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1.25 in	3.0 in

Max. Pull Tension:	25 lbs
Bulk Cable Weight:	42 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Non-Halogenated
Flammability / Fire Resistance:	UL 1685 (UL Loading-Limited Smoke), IEC 60332-1-2
NEC / UL Compliance:	800, CMG-LS
CEC / C(UL) Compliance:	CMG-LS
ICEA Compliance:	S-116-732-2013
ICEA Compliance:	S-56-434
ICEA Compliance:	S-99-689
ICEA Compliance:	S-100-685
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4

NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6
Marine Compliance:	ABS certificate 18-HS1803790-PDA
CPR Euroclass:	Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
1319SB 0101000	Black	Reel	1,000 ft	612825111825
1319SB 0105000	Black	Reel	5,000 ft	612825111832

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Print Includes Descending Footage Markings from Max. Put-Up Length to 0.
--------	---

History

Update and Revision:	Revision Number: 0.383 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.