



**Part Number: 1502P**

Media Control, 2 Cond. 18 AWG, 1 Pair 22 AWG TC, Plenum

## Product Description

Multimedia Control Cable, 1 Pair 22 AWG stranded (7x30) tinned copper (data) with foam FEP insulation, Beldfoil® shield, drain, 2 Conductor 18 AWG stranded (16x30) tinned copper conductor (power) with Flamarrest® insulation, unshielded, Plenum, Flamarrest® jacket.

## Technical Specifications

### Product Overview

Environmental Space:	Indoor - Plenum
----------------------	-----------------

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Conductors	No. of Pairs
22	7x30	TC - Tinned Copper	2	1
18	16x30	TC - Tinned Copper	2	1

Conductor Count:	4
Conductor Size:	22 AWG

#### Insulation

Element	Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness
22	FFEP - Foam Fluorinated Ethylene Propylene		0.074 in	0.0225 in
18	LS PVC - Low Smoke Polyvinyl Chloride	Flamarrest®	0.068 in	0.011 in

#### Color Chart

Number	Color
1	Blue & White
2	Red & Black

#### Inner Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	22 AWG Pair	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	24	
					TC - Tinned Copper		7x32 mm

#### Outer Shield Material

Material
Unshielded

#### Outer Jacket Material

Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness	Ripcord
LS PVC - Low Smoke Polyvinyl Chloride	Flamarrest®	0.205 in	0.015 in	Yes

## Electrical Characteristics

#### Conductor DCR

Element	Nominal Conductor DCR
22 AWG	16.3 Ohm/1000ft
18 AWG	6.9 Ohm/1000ft

## Capacitance

Element	Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
22 AWG Pair	14 pF/ft	38 pF/ft
18 AWG Pair	29 pF/ft	
22 AWG Pair		

## Inductance

Element	Nominal Inductance
22 AWG	0.232 $\mu$ H/ft
18 AWG	0.168 $\mu$ H/ft

## Impedance

Nominal Characteristic Impedance	Nominal Characteristic Impedance Description
100 Ohm	22 AWG Pair

## Current

Max. Recommended Current [A]
3.8 Amps per conductor @ 25°C (22 AWG); 7.2 Amps per conductor @ 25°C (18 AWG)

## Voltage

UL Voltage Rating
300 V RMS

## Temperature Range

Non-UL Temp Rating:	75°C
Operating Temp Range:	-20°C To +60°C

## Mechanical Characteristics

Bulk Cable Weight:	31 lbs/1000ft
Max Recommended Pulling Tension:	59.8 lbs
Min Bend Radius/Minor Axis:	2.5 in

## Standards

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
CPR Euroclass:	Eca

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

## Flammability, LSOH, Toxicity Testing

UL Flammability:	NFPA 262
CSA Flammability:	FT6

UL voltage rating:	300 V RMS
--------------------	-----------

**Plenum/Non-Plenum**

Plenum (Y/N):	Yes
---------------	-----

**Part Number**

Non-Plenum Number:	1502R
--------------------	-------

**Variants**

Item #	Color	Footnote
1502P 0101000	Black	C
1502P 8771000	Natural	C
1502P 87710000	Natural	
1502P 8775000	Natural	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2018 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.