



Product: [133084A](#)

DeviceBus®, 2 Pr #22+24 Str TC, PVC+FPE Ins, IS+OA TC Brd, PVC Jkt, SIA Armor, PVC Jkt, CM, CL2

Product Description

DeviceBus® for ODVA DeviceNet™, 2 Pair 22+24AWG (19x34+19x36) Tinned Copper, PVC+Foam PE Insulation, Individual Beldfoil® & OA Tinned Copper Braid(65%) Shield, PVC Inner Jacket, Steel Interlock Armor, PVC Outer Jacket, CM, CL2

Technical Specifications

Product Overview

Suitable Applications:	exposure to rodent, crush, or cut through force, harsh environment, ODVA device-level communication, used with CIP (common Industrial Protocol) for control, configuration, and data collection between devices, such as sensors and actuators, and higher level devices such as PLC, and PC in industrial automation, bus topology, etc.
------------------------	---

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Power Pair(s)	1	22 AWG	19x34	TC - Tinned Copper
Data Pair(s)	1	24 AWG	19x36	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Color Code
Power Pair(s)	PVC - Polyvinyl Chloride	0.021 in (0.53 mm)	Red & Black
Data Pair(s)	PE - Polyethylene (Foam)	0.026 in (0.66 mm)	Blue & White

Inner Shield

Element	Shield Type	Material	Coverage
Power Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%
Data Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Braid	Tinned Copper (TC)	65%	22 AWG (19x34) TC

Inner Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.032 in (0.81 mm)	0.280 in (7.11 mm)

Armor

Armor Type & Material
SIA - Steel Interlock Armor

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.045 in (1.1 mm)	0.573 in (14.6 mm)

Overall Cable Diameter (Nominal):	0.573 in (14.6 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
Power Pair(s)	17.5 Ohm/1000ft (57.4 Ohm/km)				4 Amps per Conductor at 25°C (Power Pair)
Data Pair(s)	28.0 Ohm/1000ft (91.9 Ohm/km)	12 pF/ft (39 pF/m)	120 Ohm	75%	4 Amps Per Conductor at 24 V (per NEC CL2) (Power Pair)

Nom. Outer Shield DCR: 3.2 Ohm/1000ft (10 Ohm/km)

High Frequency

Element	Frequency [MHz]
Data Pair(s)	0.125
	0.5
	1

Voltage

UL Voltage Rating
300 V (CM)

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C to +60°C

Max. Pull Tension: 65 lbs (29 kg)

Bulk Cable Weight: 155 lbs/1000ft (231 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor, Sunlight Resistance, Oil Resistance
Flammability / Reaction to Fire:	UL1685 FT4 Loading, FT4
NEC / UL Compliance:	Article 725, Article 800, CL2, CM
AWM Compliance:	AWM 20201, HLBCD
CEC / C(UL) Compliance:	CMG HLBCD
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	ODVA Class 2 Thin

Product Notes

Notes:	Flex Life: +/- 90 Degree Flex Test, 2" Diameter, 2 lbs. tension: 2000 Cycles minimum. Meter marks on jacket to aid users in installation. ODVA DeviceNet is an Open DeviceNet Vendor Association, Inc. trademark.
--------	---

History

Update and Revision:	Revision Number: 0.82 Revision Date: 04-08-2022
----------------------	---

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.