


Part Number: 1505S6

VideoFLEX® Snake, Banana Peel, RG59, #20-6 Coax, CMR



Product Description

20 AWG solid .032" bare copper conductors, gas-injected foam HDPE insulation, Duofoil® (100% Coverage) plus a tinned copper braid shield (95% coverage), individual PVC jackets.

Technical Specifications

Product Overview

Environmental Space:	Indoor/Outdoor
Suitable Applications:	RGB, VGA, SVGA, XGA, SXGA, UXGA, HDTV, LCD, Plasma, Digital Signage, Component Video, Video Mult, Animation, Special Effects, Suitable for use in Risers

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
20	Solid	BC - Bare Copper	0.032 in	6

Conductor Count:	6
------------------	---

Insulation

Material	Nominal Diameter
Gas-injected FHDPE - Foam High Density Polyethylene	0.145 in

Color Chart

Number	Color
1	Red
2	Green
3	Blue
4	White
5	Yellow

Inner Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Aluminum Foil-Polyester Tape-Aluminum Foil	Duofoil®	100 %
Braid	2	TC - Tinned Copper		95 %

Inner Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.235 in

Outer Jacket Material

Material	Nominal Diameter
Unjacketed	0.699 in

Construction and Dimensions

Cabling

Filler
Bonded Spline

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Inner Shield DCR	Outer Conductor DCR
10 Ohm/1000ft	10 Ohm/1000ft	3.8 Ohm/1000ft	3.8 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
16.2 pF/ft

Inductance

Nominal Inductance
0.107 μ H/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5-475 MHz	20 dB
475-525 MHz	15 dB
525-850 MHz	20 dB
850-4500 MHz	15 dB

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.3 dB/100ft
3.6 MHz	0.6 dB/100ft
10 MHz	0.9 dB/100ft
71.5 MHz	2.1 dB/100ft
135 MHz	2.7 dB/100ft
270 MHz	3.8 dB/100ft
360 MHz	4.4 dB/100ft
540 MHz	5.5 dB/100ft
720 MHz	6.4 dB/100ft
750 MHz	6.5 dB/100ft
1000 MHz	7.6 dB/100ft
1500 MHz	9.4 dB/100ft
2500 MHz	12.4 dB/100ft
3000 MHz	13.8 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.22 ns/ft	83 %

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Non-UL Temp Rating:	75°C
UL Temp Rating:	60°C
Operating Temp Range:	-35°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	208 lbs/1000ft
Max Recommended Pulling Tension:	432 lbs
Min Bend Radius/Minor Axis:	10 in

Standards

NEC/(UL) Specification:	CMR
-------------------------	-----

CEC/C(UL) Specification:	CMG
RG Type:	59/U Type
Series Type:	Series 59

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1666 Vertical Shaft
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length	Footnote
1505S6 0001000	None	612825356431	1,000 ft	C
1505S6 000500	None	612825356424	500 ft	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	US PATENT 7049523
--------	-------------------

History

Update and Revision:	Revision Number: 0.244 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.