



**Part Number: 1513C**

Audio Snake Cable, #24-12pr, TC, Individ. Shielded, CM

## Product Description

Audio Snake Cable, CM-Rated, 12-24 AWG tinned copper pairs, polyolefin insulation, individually shielded with Beldfoil® bonded to numbered/color-coded PVC jackets so both strip simultaneously, overall Beldfoil® shield, drain, flexible PVC jacket

## Technical Specifications

### Product Overview

Environmental Space:	Indoor (Not Riser or Plenum)
----------------------	------------------------------

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
24	7x32	TC - Tinned Copper	0.024 in	12

Conductor Count:	24
Total Number of Pairs:	12
Conductor Size:	24 AWG

#### Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PO - Polyolefin	0.04 in	0.007 in

#### Color Chart

Number	Color
1	Brown
2	Red
3	Orange
4	Yellow
5	Green
6	Blue
7	Purple
8	Gray
9	White
10	Black
11	Tan
12	Pink

#### Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	24	7x32 mm
				TC - Tinned Copper	

#### Inner Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.113 in	0.015 in

#### Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
------	----------	---------------------	--------------	--------------------	---------------	------------------------------

Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	18	7x26 mm
------	--------------------	-----------	-------	--------------------	----	---------

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.561 in	0.045 in	Yes

## Electrical Characteristics

#### Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR
15.9 Ohm/1000ft	23.3 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
31 pF/ft	58 pF/ft

Shielding:	Individually Shielded + Overall Shield
------------	--

#### Inductance

Nominal Inductance
0.18 µH/ft

#### Impedance

Nominal Characteristic Impedance
50 Ohm

#### Delay

Nominal Velocity of Propagation (VP) [%]
66 %

#### Current

Max. Recommended Current [A]
1.05 Amps per conductor @ 25°C

#### Voltage

UL Voltage Rating
300 V RMS

## Temperature Range

Operating Temp Range:	-35°C To +75°C
-----------------------	----------------

## Mechanical Characteristics

Bulk Cable Weight:	162 lbs/1000ft
Max Recommended Pulling Tension:	220.4 lbs
Min Bend Radius/Minor Axis:	5.75 in

## Standards

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
CPR Euroclass:	Eca

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

## Flammability, LS0H, Toxicity Testing

UL voltage rating:	300 V RMS
--------------------	-----------

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Footnote
1513C B591000	Black, Matte	C
1513C B59500	Black, Matte	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.