



Product: [1346F](#)

DeviceBus® for ODVA DeviceNet™, 2 Pr #22+24 Str TC, PVC+PO Ins, IS+OA TC Brd, TPE Jkt, CMG

Request Sample

Product Description

DeviceBus® for ODVA DeviceNet™, 2 Pair 22+24AWG (154x44+105x44) Tinned Copper, PVC+PO Insulation, Individual Beldfoil® & OA Tinned Copper Braid(65%) Shield, TPE Outer Jacket, CMG

Technical Specifications

Product Overview

Suitable Applications:	harsh environment, IIoT, factory or process automation, video, audio, data communication, etc.
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
22	154x44	TC - Tinned Copper	1
24	105x44	TC - Tinned Copper	1

Conductor Count:	4
------------------	---

Insulation

Element	Material	Nominal Wall Thickness
22 AWG	PVC - Polyvinyl Chloride	0.016 in
24 AWG	PE - Polyethylene (Foam)	0.026 in

Color Chart

Number	Color
22 AWG Pair	Red & Black
24 AWG Pair	Blue & White

Inner Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	22	26x36

Outer Shield

Type	Material	Coverage [%]
Braid	Tinned Copper (TC)	65%

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
TPE - Thermoplastic Elastomer	0.275 in	0.036 in

Electrical Characteristics

Conductor DCR

Element	Max. Conductor DCR	Nominal Conductor DCR	Nominal Outer Shield DCR
22 AWG	17.5 Ohm/1000ft		3.2 Ohm/1000ft
24 AWG	28 Ohm/100m	28.0 Ohm/1000ft	

Capacitance

Element	Nom. Capacitance Conductor to Conductor
24 AWG Pair(s)	
	12 pF/ft

Impedance

Nominal Characteristic Impedance	Nominal Characteristic Impedance Description
100 Ohm	24 AWG Pair
120 Ohm	

Delay

Max. Delay	Max. Delay Description	Nominal Velocity of Propagation (VP) [%]	Nominal Velocity of Propagation (VP) Description
1.36 ns/ft	24 AWG Pair		24 AWG Pair
		75%	

High Frequency

Element	Frequency [MHz]
24 AWG Pair Only	0.125 MHz
	0.5 MHz
	1 MHz

Current

Max. Recommended Current [A]
5 Amps per Conductor at 25°C
5 Amps per Conductor at 25°C (22 AWG)

Voltage

UL Description	UL Voltage Rating
CL2, CMG	300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temperature Range:	-30°C to +75°C

Mechanical Characteristics

Oil Resistance:	Yes
Bulk Cable Weight:	41 lbs/1000ft
Max. Pull Tension:	65 lbs
Min. Bend Radius/Minor Axis:	2.75 in

Standards

NEC Articles:	Article 800
NEC/(UL) Compliance:	CL2, CMG
CSA AWM Compliance:	AWM I/II A
CPR Euroclass:	Eca
Other Specification:	ODVA Class 2 Thin

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Oil Resistance:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4
IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
1346F T5U1000	Gray T5U	Reel	1,000 ft	612825112334

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	Hi-Flex. Thin. Meter marks on jacket to aid users in installation.
--------	--

History

Update and Revision:	Revision Number: 0.516 Revision Date: 12-19-2022
----------------------	--

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.