



**Product:** [1585A](#)

Category 5e Cable, 4 Pair, U/UTP, CMP

## Product Description

Category 5e Premise Horizontal Cable (200MHz), 4 Pair, 24 AWG Solid Bare Copper Conductors, U/UTP, Plenum-CMP, Flammarrest® PVC-LS Jacket

## Technical Specifications

### Product Overview

Suitable Applications:	Premise Horizontal Cable, Ethernet 1000BASE-T, Ethernet 100BASE-TX, Ethernet 10BASE-T, PoE++, PoE+, PoE
Patent:	This product has one or more applicable patents. More information on patents can be found at <a href="https://www.belden.com/resources/patents">https://www.belden.com/resources/patents</a> .

### Construction Details

#### Conductor

AWG	Stranding	Material	Number of Pairs
24	Solid	BC - Bare Copper	4

#### Insulation

Material	Color Code
PO+FEP - Polyolefin + Fluorinated Ethylene Propylene	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Bonded-Pair: No

#### Outer Jacket Material

Material	Material Trade Name	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	Flammarrest®	0.190 in	Yes

### Electrical Characteristics

#### Electricals

Max. Conductor DCR	Max. DCR Unbalance	Max. Capacitance Unbalance	Nom. Mutual Capacitance
93.8 Ohm/km	5%	330 pF/100m	15 pF/ft

#### Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nom. Velocity of Propagation (VP) [%]
100 MHz	537.6 ns/100m	45 ns/100m	72%

#### High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2.0 dB/100m	65.3 dB	62.3 dB	63.3 dB	60.3 dB	63.8 dB	60.8 dB	20.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
4 MHz	4.1 dB/100m	56.3 dB	53.3 dB	52.2 dB	49.2 dB	51.8 dB	48.8 dB	23.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
8 MHz	5.8 dB/100m	51.8 dB	48.8 dB	46.0 dB	43.0 dB	45.7 dB	42.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 15 Ohm
10 MHz	6.5 dB/100m	50.3 dB	47.3 dB	43.8 dB	40.8 dB	43.8 dB	40.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
16 MHz	8.2 dB/100m	47.2 dB	44.2 dB	39.0 dB	36.0 dB	39.7 dB	36.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
20 MHz	9.3 dB/100m	45.8 dB	42.8 dB	36.5 dB	33.5 dB	37.8 dB	34.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
25 MHz	10.4 dB/100m	44.3 dB	41.3 dB	33.9 dB	30.9 dB	35.8 dB	32.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 15 Ohm
31.25 MHz	11.7 dB/100m	42.9 dB	39.9 dB	31.2 dB	28.2 dB	33.9 dB	30.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 15 Ohm
62.5 MHz	17.0 dB/100m	38.4 dB	35.4 dB	21.4 dB	18.4 dB	27.9 dB	24.9 dB	21.5 dB	100 ± 15 Ohm	100 ± 15 Ohm

100 MHz	22.0 dB/100m	35.3 dB	32.3 dB	13.3 dB	10.3 dB	23.8 dB	20.8 dB	20.1 dB	100 ± 15 Ohm	100 ± 15 Ohm
155 MHz	28.1 dB/100m	32.4 dB	29.4 dB	4.4 dB	1.4 dB	20.0 dB	17.0 dB	18.8 dB		
200 MHz	32.4 dB/100m	30.8 dB	27.8 dB	4.0 dB	1.0 dB	17.8 dB	14.8 dB	18.0 dB		

#### Voltage

<b>UL Voltage Rating</b>
300 V (CMP)

### Mechanical Characteristics

#### Temperature

UL Rating	Operating	Installation	Storage
75°C	-20°C To +75°C	0°C To +50°C	-20°C To +75°C

#### Bend Radius

Stationary Min.	Installation Min.
1.0 in	2.0 in

Max. Pull Tension:	25 lbs
Bulk Cable Weight:	21 lbs/1000ft

### Standards and Compliance

Environmental Suitability:	Plenum, Indoor
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Fire Resistance:	NFPA 262, UL 910 (Plenum), FT6, FT6, IEC 60332-1-2
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
ICEA Compliance:	S-90-661-2012
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3
NEMA Compliance:	NEMA WC-63.1
Data Category:	Category 5e
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 5e
CPR Euroclass:	Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
APAC Compliance:	China RoHS II (GB/T 26572-2011)

### Part Number

Non-Plenum Number:	1583A
--------------------	-------

#### Variants

Item #	Color	Putup Type	Length	UPC
1585A 010500	Black	Reel	500 ft	612825118404
1585A 0101000	Black	Reel	1,000 ft	612825118398
1585A 010U1000	Black	UnReel	1,000 ft	612825118381
1585A D151000	Blue	Reel	1,000 ft	612825118244
1585A D15U1000	Blue	UnReel	1,000 ft	612825118237
1585A D153000	Blue	Reel	3,000 ft	612825118251
1585A 0081000	Gray	Reel	1,000 ft	612825118350
1585A 008U1000	Gray	UnReel	1,000 ft	612825118343
1585A 0051000	Green	Reel	1,000 ft	612825118336
1585A 005U1000	Green	UnReel	1,000 ft	612825118329
1585A 8771000	Natural	Reel	1,000 ft	612825118442
1585A 877U1000	Natural	UnReel	1,000 ft	612825118435
1585A 0031000	Orange	Reel	1,000 ft	612825118299
1585A 003U1000	Orange	UnReel	1,000 ft	612825118282
1585A 0121000	Pink	Reel	1,000 ft	612825118428
1585A 012U1000	Pink	UnReel	1,000 ft	612825118411
1585A 0021000	Red	Reel	1,000 ft	612825118275
1585A 002U1000	Red	UnReel	1,000 ft	612825118268
1585A 0091000	White	Reel	1,000 ft	612825118374

1585A 009U1000	White	UnReel	1,000 ft	612825118367
1585A 0041000	Yellow	Reel	1,000 ft	612825118312
1585A 004U1000	Yellow	UnReel	1,000 ft	612825118305

## Product Notes

Notes: Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Values above 100 MHz are for Engineering Information Only. Print Includes Descending Footage Markings from Max. Put-Up Length to 0.

## History

Update and Revision: Revision Number: 0.407 Revision Date: 02-16-2021

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.