



Product: [1407B](#)



RGB Video, High Flex, #26-4 Coax Stranded BC

Product Description

RGB Video Coax, 4-26 AWG stranded bare copper conductors, foam HDPE insulation, Duofoil® +95% tinned copper braid shield, inner PVC jackets, flexible PVC jacket

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
26	7x34	BC - Bare Copper	0.019 in	4

Conductor Count: 4

Insulation

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.089 in

Color Chart

Number	Color
1	Red
2	Green
3	Blue
4	White

Inner Shield

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Tinned Copper (TC)		95%

Inner Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.146 in

Outer Shield

Material
No Shield

Outer Jacket

Material	Nominal Diameter	Separator Material
PVC - Polyvinyl Chloride	0.435 in	Polyester Tape

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Inner Shield DCR	Outer Conductor DCR
41.5 Ohm/1000ft	41.5 Ohm/1000ft	8.6 Ohm/1000ft	8.6 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Other Conductor to Shield
17.3 pF/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
10-40 MHz	25 dB

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.6 dB/100ft
5 MHz	1.3 dB/100ft
10 MHz	1.8 dB/100ft
30 MHz	3.1 dB/100ft
50 MHz	3.9 dB/100ft
100 MHz	5.4 dB/100ft
200 MHz	7.5 dB/100ft
400 MHz	10.4 dB/100ft
700 MHz	13.5 dB/100ft
900 MHz	15.2 dB/100ft
1000 MHz	15.9 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.3 ns/ft	78%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)
30 MHz	3.6 dB/100ft

Voltage

Non-UL Voltage Rating
300 V RMS

Temperature Range

Non-UL Temp Rating:	60°C
Operating Temperature Range:	-40°C To +60°C

Mechanical Characteristics

Bulk Cable Weight:	93 lbs/1000ft
Max. Pull Tension:	138 lbs
Min. Bend Radius/Minor Axis:	4.5 in

Standards

RG Type:	Mini 59
Series Type:	59

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
MII Order #39 (China RoHS):	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
1407B J5C1000	Black, Vivid Matte	Reel	1,000 ft	612825355090

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.332 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.