



**Product:** [1633ENH](#)

Cat 5e Cable, F/UTP, LSZH, 4 Pair, AWG 24, Indoor CPR Dca

## Product Description

Cat. 5e (100MHz), 4-Pair, F/UTP Foil shielded, Premise Horizontal Cable, 24 AWG solid bare copper conductors, Polyethylene insulation, Beldfoil® shield, AWG 26 solid tinned copper drainwire, LSZH jacket, RJ-45 compatible

## Technical Specifications

### Product Overview

Suitable Applications:	Horizontal and building backbone cable; Support current and future Category 5e applications, such as: 1000Base-T (Gigabit Ethernet), 100 Base-T, 10 Base-T, FDDI, ATM
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

#### Insulation

Type	Material	Nominal Diameter
Dielectric	PO - Polyolefin	1.05 mm

Bonded-Pair:	No
--------------	----

#### Color Chart

Number	Color
Pair 1	White/Blue & Blue
Pair 2	White/Green & Green
Pair 3	White/Orange & Orange
Pair 4	White/Brown & Brown

#### Outer Shield Material

Type	Material	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D	Drainwire Position
Tape	Bi-Laminate (Alum+Poly)	100%	TC - Tinned Copper	26	Solid	Over foil

Table Notes:	Aluminum facing outside in contact with drain wire
--------------	--

#### Outer Jacket Material

Material	Nominal Diameter	Diameter +/- Tolerance
LSZH - Low Smoke Zero Halogen (Flame Retardant)	6.0 mm	0.3 mm

### Construction and Dimensions

Min Elongation at Breakof Conductors:	10 %
Min Elongation at Breakof Insulation:	100 %
Min Elongation at Breakof Jacket:	100 %
Min Tensile Strength of Jacket:	9 MPa

### Electrical Characteristics

## Conductor DCR

Max. Conductor DCR	Max DCR Unbalanced Between Pairs [%]	Max. DCR Unbalanced Within Pair [%]
95 Ohm/km	4 %	2 %

## Capacitance

Max. Capacitance Unbalance	Max. Mutual Capacitance
1,600 pF/m	56 pF/m

## Impedance

Nominal Characteristic Impedance
100 Ohm

## Delay

Max. Delay Skew	Min. Velocity of Propagation
40 ns/100m	60%

## High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.1 dB/100m	65.3 dB	62.3 dB	63.2 dB	60.2 dB	64 dB	61 dB	20 dB	40 dB	35 dB
4 MHz	4 dB/100m	56.3 dB	53.3 dB	52.32 dB	49.3 dB	52 dB	49 dB	23 dB	34 dB	23 dB
10 MHz	6.3 dB/100m	50.3 dB	47.3 dB	44 dB	41 dB	44 dB	41 dB	25 dB	30 dB	15 dB
16 MHz	8 dB/100m	47.2 dB	44.2 dB	39.2 dB	36.2 dB	39.9 dB	36.9 dB	25 dB	28 dB	10.9 dB
20 MHz	9 dB/100m	45.8 dB	42.8 dB	36.8 dB	33.8 dB	38 dB	35 dB	25 dB	27 dB	9 dB
31.25 MHz	11.4 dB/100m	42.9 dB	39.9 dB	31.5 dB	28.5 dB	34.1 dB	31.5 dB	23.6 dB	25.1 dB	5.5 dB
62.5 MHz	16.5 dB/100m	38.4 dB	35.4 dB	21.9 dB	18.9 dB	28.1 dB	25.1 dB	21.5 dB	22 dB	
100 MHz	21.3 dB/100m	35.3 dB	32.3 dB	14 dB	11 dB	24 dB	21 dB	20.1 dB	20 dB	

Table Notes:	Limits below 4 MHz are for information only. Reference standard: IEC 61156-5
General Electrical Parameters Notes:	Reference standard: ISO/IEC 61156-5
Coupling Attenuation Class:	Type II
Segregation class according EN50174-2:	c

## Transfer Impedance

Frequency [MHz]	Description	Transfer Impedance
1 Mhz	Grade 2	Max. 50 mOhm/m
10 Mhz		Max. 100 mOhm/m
30 Mhz		Max. 200 mOhm/m
100 Mhz		Max. 1000 mOhm/m

## Current

Max. Recommended Current [A]
1.5 Amps per Conductor

## Voltage

Voltage Rating [V]
72 V

## Temperature Range

Installation Temp Range:	0°C To +50°C
Operating Temp Range:	-30°C To +60°C

## Mechanical Characteristics

Bulk Cable Weight:	39 kg/km
Max. Pull Tension:	72 N
Min Bend Radius During Installation:	48 mm
Min Bend Radius During Operation:	24 mm

## Standards

IEC Compliance:	ISO/IEC 11801-1
CPR Euroclass:	Dca-s2,d2,a1
CENELEC Compliance:	EN 50173-1
Data Category:	Category 5e

ANSI Compliance:	ANSI/TIA 568.2-D (2018)
IEEE Compliance:	PoE: IEEE 802.3bt Type 1, Type 2, Type 3

## Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Dca
EU RoHS Compliance Date (yyyy-mm-dd):	2005-01-01

## Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
Burning Load:	440 kJ/m
IEC 60754-1 (EN50267-1)- Halogen Amount:	Zero
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 (EN 61034-2) (VDE 0482-1034) - Smoke Density Min. Transmittance:	IEC 61034-2

## Part Number

### Variants

Item #	Color	Putup Type	Length	EAN
1633ENH.07305	Black	Reel	305 m	8719605169075
1633ENH.01B100	Blue	Flat Box	100 m	8719605002884
1633ENH.01305	Blue	Reel	305 m	8719605002860
1633ENH.01500	Blue	Reel	500 m	8719605002877
1633ENH.00B100	Gray	Flat Box	100 m	8719605002853
1633ENH.00305	Gray	Reel	305 m	8719605002839
1633ENH.00500	Gray	Reel	500 m	8719605002846
1633ENH.001000	Gray	Reel	1,000 m	8719605002815
1633ENH.002050	Gray	Reel	2,050 m	8719605002822
1633ENH.03305	Green	Reel	305 m	8719605002907
1633ENH.02305	Orange	Reel	305 m	8719605002891
1633ENH.04305	Red	Reel	305 m	8719605002914
1633ENH.041000	Red	Reel	1,000 m	8719605169082
1633ENH.05305	Yellow	Reel	305 m	8719605002921

## Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system.
--------	--

## History

Update and Revision:	Revision Number: 0.255 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.