



**Part Number: 1694A**

Serial Digital Coax, RG6 Type, #18 Solid BC, Duofoil® + 95% TC braid, CMR

## Product Description

Low Loss Serial Digital Coax, Riser-CMR, RG6 Type, 18 AWG solid bare copper conductor, foam HDPE core, Duobond® +95% tinned copper braid, PVC jacket

## Technical Specifications

### Product Overview

Environmental Space:	Outdoor - Aerial
Suitable Applications:	SMPTE 2081-1 6 Gb/s UHDTV, SMPTE 424M 3 Gb/s HD-SDI 1080p

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
18	Solid	BC - Bare Copper	0.04 in	1

Conductor Count:	1
Conductor Size:	18 AWG

#### Insulation

Material	Nominal Diameter
Gas-injected FHDPE - Foam High Density Polyethylene	0.18 in

#### Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Aluminium / Polyester / Aluminium	Duofoil®	100 %
Braid	2	TC - Tinned Copper		95.0 %

#### Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.274 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Outer Conductor DCR
6.4 Ohm/1000ft	2.8 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Shield
16.2 pF/ft

#### Inductance

Nominal Inductance
0.106 µH/ft

#### Impedance

Nominal Characteristic Impedance
75 Ohm

#### Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5 - 1600 MHz	23 dB
1600 - 4500 MHz	21 dB
4500 - 6000 MHz	15 dB

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.24 dB/100ft
3.58 MHz	0.44 dB/100ft
5 MHz	0.52 dB/100ft
6 MHz	0.57 dB/100ft
7 MHz	0.61 dB/100ft
10 MHz	0.71 dB/100ft
12 MHz	0.78 dB/100ft
25 MHz	1.08 dB/100ft
67.5 MHz	1.65 dB/100ft
71.5 MHz	1.69 dB/100ft
88.5 MHz	1.86 dB/100ft
100 MHz	1.95 dB/100ft
135 MHz	2.24 dB/100ft
143 MHz	2.3 dB/100ft
180 MHz	2.57 dB/100ft
270 MHz	3.17 dB/100ft
360 MHz	3.69 dB/100ft
540 MHz	4.5 dB/100ft
720 MHz	5.3 dB/100ft
750 MHz	5.4 dB/100ft
1000 MHz	6.3 dB/100ft
1500 MHz	7.8 dB/100ft
2000 MHz	9.2 dB/100ft
2250 MHz	9.8 dB/100ft
3000 MHz	11.5 dB/100ft
4500 MHz	14.5 dB/100ft
6000 MHz	17.7 dB/100ft

#### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.24 ns/ft	82 %

#### Voltage

UL Voltage Rating
300 V RMS

Electrical Characteristics Notes:	Return Loss: Fixed bridge and termination
-----------------------------------	---

#### Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-30°C To +75°C

#### Mechanical Characteristics

UV Resistance:	Yes
Bulk Cable Weight:	41 lbs/1000ft
Max Recommended Pulling Tension:	69 lbs
Min Bend Radius/Minor Axis:	2.75 in

#### Standards

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
CPR Euroclass:	Eca
RG Type:	6/U Type

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

### Suitability

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only

### Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1666 Vertical Shaft
CSA Flammability:	FT4
UL voltage rating:	300 V RMS

### Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	1695A

### Part Number

Related Parts:	1694ABHD1, 1694ABHD3, 1694ABHDL
----------------	---------------------------------

### Variants

Item #	Color	Footnote
1694A.001000	Black	
1694A.001372	Black	
1694A.00152	Black	
1694A.00305	Black	
1694A.00500	Black	
1694A 0101000	Black	C
1694A 010500	Black	C
1694A 0105000	Black	C N
1694A 010N1000	Black	
1694A 010N1000	Black	
1694A 0061000	Blue, Light	C
1694A 0065000	Blue, Light	C N
1694A.051372	Blue, RAL 5015	
1694A.05305	Blue, RAL 5015	
1694A 0011000	Brown	C
1694A 0015000	Brown	C N
1694A.09500	Cream	
1694A 0081000	Gray	C
1694A 0085000	Gray	C N
1694A.081372	Gray, Slate	
1694A.08305	Gray, Slate	
1694A.061219	Green	
1694A.061372	Green	
1694A.06152	Green	
1694A.06305	Green	
1694A.064000	Green	
1694A N3U1000	Green, Mil	C
1694A N3U5000	Green, Mil	C N
1694A N3UN1000	Green, Mil	

1694A N3UN1000	Green, Mil	
1694A 0031000	Orange	C
1694A.031372	Orange, RAL 2003	
1694A.03305	Orange, RAL 2003	
1694A 0021000	Red	C
1694A 0025000	Red	C N
1694A.011372	Red, RAL 3000	
1694A.01305	Red, RAL 3000	
1694A.021372	Violet	
1694A.02305	Violet	
1694A 0071000	Violet	C
1694A 0075000	Violet	C N
1694A.021000	Violet	
1694A 007N1000	Violet	
1694A 007N1000	Violet	
1694A.071372	White	
1694A.07305	White	
1694A 0091000	White	C
1694A 009N1000	White	
1694A 009N1000	White	
1694A 0041000	Yellow	C
1694A 004N1000	Yellow	
1694A 004N1000	Yellow	
1694A.041372	Yellow, RAL 1021	
1694A.04305	Yellow, RAL 1021	

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	N - FINAL PUT-UP LENGTH MAY VARY -0% TO +10% FROM LENGTH SHOWN.

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.