

Product: [1512ENH](#) 



AUDIO ANALOG 8 PAIR 24AWG, BELDFOIL, LSZH

Product Description

ANALOG AUDIO 8 PAIR 24AWG/0.22mm², BELDFOIL, LSZH

Technical Specifications

Product Overview

Suitable Applications:	8-pair 24AWG halogen-free multi-core cable; For analogue audio
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Construction n x D
24	7x32	TC - Tinned Copper	7x0.20 mm

Conductor Count:	16
Total Number of Pairs:	8

Insulation

Type	Material	Nominal Diameter	Diameter +/- Tolerance
Insulation	PE - Polyethylene	1.02 mm	0.05 mm

Color Chart

Number	Color
Pair 1 t/m 8	Red & Black

Inner Shield

Type	Material	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D	Drainwire Position
Tape	Bi-Laminate (Alum+Poly)	100%	Stranded tinned copper	24	7x0.20 mm	Under shielding foil

Table Notes:	Aluminum inside
--------------	-----------------

Inner Jacket

Material	Nominal Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	2.86 mm

Table Notes:	Jacket single element, elements are numbered 1 - 8
--------------	--

Outer Shield

Type	Material	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	100%	TC - Tinned Copper	7xAWG26	7x0.40 mm

Outer Jacket

Material	Nominal Diameter	Diameter +/- Tolerance	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	11.70 mm	0.40 mm	1.00 mm

Construction and Dimensions

Cabling

Description

1 filler + 8 pairs

Min Elongation at Breakof Jacket:	125 %
Min Tensile Strength of Jacket:	9 MPa

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Nominal Inner Shield DCR
88.5 Ohm/km	52 Ohm/km

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
92 pF/m	180 pF/m

Inductance

Nominal Inductance
0.75 μ H/m

Temperature Range

Other Temp Range:	-30 to +70 °C
-------------------	---------------

Mechanical Characteristics

Max. Pull Tension:	610 N
Min. Bend Radius During Installation:	175 mm
Min. Bend Radius During Operation:	115 mm

Standards

CPR Euroclass:	Eca
CENELEC Compliance:	EN 50290-2-20

Applicable Environmental and Other Programs

Environmental Space:	Indoor
----------------------	--------

Flammability, LS0H, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
IEC 60754-1 - Halogen Amount:	Zero
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	2.5 μ S/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 - Smoke Density Min. Transmittance:	60%

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	EAN
1512ENH.00500	Gray	Reel	500 m	8719605001771
1512ENH.001000	Gray	Reel	1,000 m	8719605001757

History

Update and Revision:	Revision Number: 0.200 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.