




Product: [1515C](#)



Audio Snake Cable, #24-20pr, TC, Indiv. Shielded, CM

Product Description

Audio Snake Cable, CM-Rated, 20-24 AWG tinned copper pairs, polyolefin insulation, individually shielded with Beldfoil® bonded to numbered/color-coded PVC jackets so both strip simultaneously, overall Beldfoil® shield, drain, flexible PVC jacket

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
24	7x32	TC - Tinned Copper	0.024 in	20

Conductor Count:	40
Total Number of Pairs:	20

Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PP - Polypropylene	0.04 in	0.008 in

Color Chart

Number	Color
1	Brown
2	Red
3	Orange
4	Yellow
5	Green
6	Blue
7	Purple
8	Gray
9	White
10	Black
11	Tan
12	Pink
13	Gray/Brown
14	Gray/Red
15	Gray/Orange
16	Gray/Yellow
17	Gray/Green
18	Gray/Blue
19	Gray/Purple
20	Gray/Gray

Color Chart 2

Color
Red and Black

Inner Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire Diameter	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	0.024 in	24	7x32

Inner Jacket

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.113 in	0.015 in

Outer Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire Diameter	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	0.046 in	18	7x26

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.71 in	0.055 in	Yes

Electrical Characteristics

Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance
15.9 Ohm/1000ft	23.3 Ohm/1000ft	23.3 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
31 pF/ft	58 pF/ft

Inductance

Nominal Inductance
0.18 µH/ft

Delay

Nominal Velocity of Propagation (VP) [%]
66%

Current

Max. Recommended Current [A]
1.05 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Operating Temperature Range:	-35°C To +75°C
------------------------------	----------------

Mechanical Characteristics

Bulk Cable Weight:	264 lbs/1000ft
Max. Pull Tension:	352.4 lbs
Min. Bend Radius/Minor Axis:	7.25 in

Standards

NEC/(UL) Compliance:	CM
CEC/C(UL) Compliance:	CM

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)

EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

UL voltage rating:	300 V RMS
--------------------	-----------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
1515C B59500	Black, Matte	Reel	500 ft	612825116899
1515C B591000	Black, Matte	Reel	1,000 ft	612825116882

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.344 Revision Date: 11-27-2023
----------------------	--

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.