



**Product:** [16P0.5YCY](#)

MachFlex™ LiYCY(TP), 16 Pr 0.5mm<sup>2</sup> Str BC, PVC Ins, TCBS, PVC Jkt

## Product Description

MachFlex™ LiYCY(TP) Control VDE Certified & Twisted Pair PVC Signal Cables 16 Pair 0.5mm<sup>2</sup> Stranded Bare Copper, PVC Insulation, Tinned Copper Braid Shield, PVC Jacket

## Technical Specifications

### Product Overview

**Suitable Applications:** Designed for applications which are installed in occasional flexing and fixed locations. Cable applications include precision control sensors, pressure gauge, temperature controllers, control panels, vibration monitoring systems, intelligent security controllers, production machinery and many more. Tinned copper braid shield ensure the cables with excellent noise immunity. Twisted pair (TP) design reduced crosstalk effects

### Physical Characteristics (Overall)

#### Conductor

Element	AWG	Stranding	Material	No. of Conductors
Conductor(s)	0.5 mm <sup>2</sup>	Stranded	BC - Bare Copper	32

Conductor Count: 32

#### Insulation

Material
PVC - Polyvinyl Chloride

#### Color Chart

Number	Color
1	White, Brown
2	Green, Yellow
3	Gray, Pink
4	Blue, Red
5	Black, Violet
6	Gray with Pink strips, Red with Blue strips
7	White with Green strips, Brown with Green strips
8	White with Yellow strips, Yellow with Brown strips
9	White with Gray strips, Gray with Brown strips
10	White with Pink strips, Pink with Brown strips
11	White with Blue strips, Brown with Blue strips
12	White with Red strips, Brown with Red strips
13	White with Black strips, Brown with Black strips
14	Gray with Green strips, Yellow with Gray strips
15	Pink with Green strips, Yellow with Pink strips
16	Green with Blue strips, Yellow with Blue strips

#### Outer Shield

Type	Material
Braid	Tinned Copper (TC)

#### Outer Jacket

Material	Nominal Diameter
----------	------------------

PVC - Polyvinyl Chloride 16.2 mm

## Electrical Characteristics

### Conductor DCR

Max. Conductor DCR
39 Ohm/km

### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
120 pF/m	160 pF/m

Insulation Resistance: 20 GOhm x cm

Min Insulation Resistance: 20 GOhm x cm

### Inductance

Nominal Inductance
0.5 µH/m

### Voltage

Description	Voltage Rating [V]
Operating Voltage	500 V
Testing Voltage	1500 V

## Temperature Range

Installation Temp Range: 40°C to +80°C

Operating Temp Range: 5°C to +70°C

## Mechanical Characteristics

UV Resistance: Yes

Bulk Cable Weight: 352 kg/km

Min. Bend Radius During Installation: 6 x OD

Min. Bend Radius During Operation: 15 x OD

## Standards

Other Specification: IEC 60228, DIN EN 50290222, VDE 0812, DIN VDE 020736341, DIN 47100, DIN VDE 0295, BS 6360

## Applicable Environmental and Other Programs

EU Directive 2011/65/EU (RoHS 2): Compliant

## Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes

Suitability - Sunlight Resistance: Yes

## Flammability, LSOH, Toxicity Testing

IEC Flammability: IEC 60332-1-2

Other Flammability: DIN VDE 0482-332-1-2, DIN EN 60332-1-2

## Related Part Numbers

### Variants

Item #	Color	Length
16C0.5YCY 010305M	Black, RAL 9005	305 m
16C0.5YCY 010500M	Black, RAL 9005	500 m
16C0.5YCY F2V305M	Gray, RAL 7032	305 m
16C0.5YCY F2V500M	Gray, RAL 7032	500 m

## History

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.