




Product: [1801BD](#) 

Audio Snake Cable, 2 Pair 24 AWG, TC, Individually Shielded, CMP

Product Description

Digital Audio Snake Cable, Plenum-CMP, 2-24 AWG tinned copper pairs, foam FEP insulation, Flamarrest® jacket, Parallel construction

Technical Specifications

Product Overview

Suitable Applications:	Recording Studio, Radio Broadcast, Sports Stadium, Nurse Call
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
24	7x32	TC - Tinned Copper	0.024 in	2

Conductor Count:	4
------------------	---

Insulation

Material	Material Trade Name	Nominal Diameter
FEP - Fluorinated Ethylene Propylene (Foam)	Teflon®	0.066 in

Color Chart

Number	Color
1	Red & Black
2	White & Blue

Inner Shield

Type	Material	Material Trade Name	Drainwire Material	Drainwire AWG
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	TC - Tinned Copper	24

Outer Shield

Material	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Bi-Laminate (Alum+Poly)	100%	TC - Tinned Copper	24	7x32

Outer Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.165 x 0.345 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
23.7 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
12 pF/ft	26 pF/ft

Inductance

Nominal Inductance0.18 μ H/ft**Impedance****Nominal Characteristic Impedance**

110 Ohm

High Frequency (Nominal/Typical)**Nom. Insertion Loss**

0.82 dB/100ft

1.01 dB/100ft

1.02 dB/100ft

1.08 dB/100ft

1.15 dB/100ft

1.16 dB/100ft

1.23 dB/100ft

1.34 dB/100ft

1.38 dB/100ft

1.58 dB/100ft

1.79 dB/100ft

1.85 dB/100ft

2.05 dB/100ft

2.34 dB/100ft

2.43 dB/100ft

3.33 dB/100ft

Delay**Nominal Velocity of Propagation (VP) [%]**

78%

High Frequency**Frequency [MHz]**

0.384 MHz

0.7056 MHz

0.768 MHz

1.024 MHz

1.4112 MHz

1.536 MHz

2.048 MHz

2.8224 MHz

3.072 MHz

4.096 MHz

5.6448 MHz

6.144 MHz

8.192 MHz

11.2896 MHz

12.288 MHz

24.576 MHz

Current**Max. Recommended Current [A]**

2.9 Amps per Conductor at 25°C

Voltage**UL Voltage Rating**

300 V RMS

Temperature Range

Operating Temperature Range: -20°C To +60°C

Mechanical Characteristics

UV Resistance: No

Bulk Cable Weight:	26 lbs/1000ft
Max. Pull Tension:	33 lbs
Min. Bend Radius/Minor Axis:	1.75 in

Standards

NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP
Other Specification:	AES/EBU

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Plenum
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT6
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
1801BD 8771000	Natural	Reel	1,000 ft	612825122982
1801BD Z4B1000	Violet Z4B	Reel	1,000 ft	612825122975

Product Notes

Notes:	Teflon [®] is a registered trademark of Chemours and is used under license by Belden, Inc.
--------	---

History

Update and Revision:	Revision Number: 0.368 Revision Date: 04-08-2022
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.