




Product: [1801BS6](#)



Audio Snake Cable, #24-6pr, TC, Individ. Shielded, CMP

### Product Description

Digital Audio Snake Cable, Plenum-CMP, 6-24 AWG tinned copper pairs, foam FEP insulation, individually shielded with Beldfoil® bonded to numbered/color-coded Flammarrest® jackets so both strip simultaneously, Banana Peel construction

### Technical Specifications

#### Product Overview

Suitable Applications:	Recording Studio, Radio Broadcast, Sports Stadium, Nurse Call
------------------------	---

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	6	24 AWG	7x32	TC - Tinned Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	FEP - Fluorinated Ethylene Propylene (Foam)	0.02 in (0.51 mm)	0.066 in (1.7 mm)	White and Blue and Numbered

##### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

##### Outer Jacket

Material	Nom. Diameter
Banana Peel (No Overall Jacket)	0.495 in

Overall Cable Diameter (Nominal):	0.495 in
-----------------------------------	----------

#### Electrical Characteristics

##### Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
28.8 Ohm/1000ft	12 pF/ft (39 pF/m)	26 pF/ft (85 pF/m)	110 Ohm	78%	2.75 Amps per Conductor at 25°C

##### Voltage

<b>UL Voltage Rating</b>
300 V

#### Mechanical Characteristics

##### Temperature

Operating	Installation
-20°C to +60°C	0°C To +60°C

##### Bend Radius

Stationary Min.	Installation Min.

4.95 in (126 mm)	4.95 in
------------------	---------

Max. Pull Tension:	100 lbs (45 kg)
Bulk Cable Weight:	95lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Flammability / Reaction to Fire:	FT6
NEC / UL Compliance:	CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	AES/EBU

## Product Notes

Notes:	Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.
--------	---

## History

Update and Revision:	Revision Number: 0.351 Revision Date: 05-31-2024
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC
1801BS6 8771000	Natural	Reel	1,000 ft	612825123026
1801BS6 Z4B1000	Vio Z4B	Reel	1,000 ft	612825123019

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.