



Product: [1816R](#)

Audio Snake Cable, 6 Pr #22 Str TC, Ind. Shielded & Jacketed, O/A Foil, PVC Jkt, CMR

Product Description

Audio Snake Cable, 6 Pair 22 AWG (7 x 30) Tinned Copper, PP Insulation, Individually Foil Shielded and PVC Jacketed, Overall Beldfoil® Shield, PVC Jacket, Ripcord, CMR

Technical Specifications

Product Overview

Suitable Applications:	Multi-channel interconnect between audio equipment such as microphones, speakers, amplifiers, mixing consoles; Live events or studio sound; Analog audio
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	6	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PP - Polypropylene	0.010 in (0.25 mm)	0.05 in (1.3 mm)	Black, Red

Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type	Notes
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC	Individual pair tapes are adhered to their inner jackets for easy stripping

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (19x30) TC

Inner Jacket

Element	Material	Nom. Diameter
Pair(s)	PVC - Polyvinyl Chloride	0.133 in (3.38 mm)

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.030 in (0.76 mm)	0.462 in (11.7 mm)	Yes

Overall Cable Diameter (Nominal):	0.462 in (11.7 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Pair(s)	14.8 Ohm/1000ft (48.6 Ohm/km)	31 pF/ft (100 pF/m)	56 pF/ft (180 pF/m)	50 Ohm	66%	2.0 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V (CMR)

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C	-30°C to +60°C

Bend Radius

Stationary Min.	Installation Min.
4.6 in (120 mm)	4.6 in (120 mm)

Max. Pull Tension:	131 lbs (59.4 kg)
Bulk Cable Weight:	120 lbs/1000ft (180 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor, Outdoor - Black only, Aerial - Black only, When supported by messenger wire
Flammability / Reaction to Fire:	UL1666 Riser, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMR
European Directive Compliance:	EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	1816P

History

Update and Revision:	Revision Number: 0.393 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1816R 010500	Black	Reel	500 ft	612825123552	C
1816R 0101000	Black	Reel	1,000 ft	612825123545	C
1816R 0102000	Black	Reel	2,000 ft	612825438281	
1816R 0104000	Black	Reel	4,000 ft	612825438298	
1816R 0105000	Black	Reel	5,000 ft	612825438182	

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.