



Product: [16-E1-L - S30924-Q1215-X101](#) 

XTran Interface Module with 16x E1 LAN ports

Product Description

The 16-E1-L interface module (=IFM) provides sixteen E1 ports for connecting E1 TDM links to the XTran network. 16-E1-L refers to '16 ports – E1 – LAN'. E1 links are used to implement synchronous TDM links between two end points. These links typically transport voice and/or data using TDM. This IFM converts the E1 framing from an E1 link into MPLS-TP packets over the XTran network, and vice versa. A packetized TDM service is called a Circuit Emulation Service (=CES). A maximum of 64 CESes (with a maximum of 32 Hitless switching services) can be configured per 16-E1-L module.

Technical Specifications

Product Overview

Product Category:	Legacy Interface Card
Name:	S30924-Q1215-X101
Part Number:	S30924-Q1215-X101
Port Type and Quantity:	1x HPDB68 Connector
Port Mode:	LAN

Product Life Cycle

Life Cycle:	Active - Product is available
-------------	-------------------------------

Power requirements

Operating Voltage:	+12V
Power Consumption:	Measured at 25°C/77°F, with data transport: 9.2W

Features and Protocols

Synchronization:	Sync-E
Test & Debugging Features:	Test & Loopback, Loss Measurement (LM) (in aggregation/access nodes), Delay Measurement (DM) (in aggregation/access nodes), Tunnel Ping, Tunnel Traceroute, Port Mirroring (can only be a source, can be mirrored to Ethernet IFMs)
Configurable Services:	Circuit Emulation: SAToP (=Structured Agnostic TDM over Packet), CESoPSN (=Circuit Emulation Service over Packet Switched Network), Hitless Switching / Single Path, Channelized SDH-SONET (CSoP Smart SFP) for STM-1

Ambient conditions

MTBF (Telcordia SR-332 Issue 4) @ 25°C:	147 Years
Operating Temperature Range:	With XT-1104-A, XT-2206-A, XT-2209-A, XT-2210-A (aggregation nodes): -30° to +65°C (-22° to 149°F); With XT-2215-A (core nodes): -20° to +55°C (-4° to 131°F)
Storage Temperature Range:	-30° to +75°C (-22° to 167°F)
Relative humidity (non-condensing):	0-95 %

Mechanical Construction

Overall Width:	20.32 mm
Overall Height:	126 mm
Overall Depth:	195 mm
Weight:	0.234 kg

Approvals

Basis Standard:	CE, EN 55032:2015 + A11:2020, EN IEC 61000-3-2:2019, EN 61000-3-3:2013 + A2 :2021, EN 55035:2017 + A11:2020, EN IEC 61000-6-1:2019, EN IEC 61000-6-2:2019, EN IEC 61000-6-3:2021, EN IEC 61000-6-4:2019
-----------------	---

Safety of industrial control equipment:	EN 62368-1:2014
Power Utility:	EN 61000-6-5:2015, EN 61850-3:2014 (§6.7), IEEE 1613-2009 (§4), IEEE1613-2013 (clause 5,7,8,9,10)
Transportation:	EN 50121-4:2016 + A1:2019

Reliability

Guarantee:	Standard 1 year (extension possible)
------------	--------------------------------------

Scope of delivery and accessories

Accessories to Order Separately:	Interface Adapter Kit for Core Nodes: C30965-A9550-D16; Dropcable, 1.5m HPDB68 to open end for 16-E1-L (1 per 16 port card): V30912-A3064-A3; Dropcable, 2m HPDB68 to 16 RJ45 with coupler for 16-E1-L (1 per 16 port card): C30965-A9550-D11; Patch panel 1HU feedthrough 24 ports (for A9550-D11): V30912-A3010-A5; BNC Patch panel with Drop cable, 2m HPDB68 to 16 Port Coax (1 per 16 port card): C30965-A9550-D14
----------------------------------	---

Further Instructions

Product Documentation:	Available via Belden Solutions Portal site
Certificates:	Available via Belden Solutions Portal site
Software Download:	Available via Belden Solutions Portal site

History

Update and Revision:	Revision Number: 0.3 Revision Date: 08-04-2026
----------------------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.