


Product: [1671A](#) 

Conformable Coax, 50 Ohm RG-405, 24 AWG Solid SCCS, Copper-Tin Composite Shield, Unjacketed



REPRESENTATIVE IMAGE

Product Description

Conformable Coax, 50 Ohm, RG-405, 24 AWG Solid Silvered Copper Covered Steel Conductor, PTFE Insulation, Copper Tape + 100% Tin-Filled Composite Braid Shield, Unjacketed

Technical Specifications

Product Overview

Suitable Applications:	Microwave and other high frequency applications, Interconnect RF equipment, Radar equipment, Military communications
------------------------	--

Construction Details

RG Type:	405
----------	-----

Conductor

AWG	Stranding	Nom. Diameter	Material
24	Solid	0.020 in	SCCS - Silvered Copper Covered Steel

Insulation

Material	Nom. Diameter
PTFE - Polytetrafluoroethylene	0.062 in

Outer Shield Material

Layer	Outer Shield Type	Material	Coverage	Notes
1	Tape	Bare Copper (BC)	100%	
2	Braid	Tinned Copper (TC + Tin Filled)	100%	Diameter: 0.085 inch

Electrical Characteristics

VSWR

Frequency [MHz]	Max. VSWR
500 MHz	1.1:1
1000 MHz	1.11:1
3000 MHz	1.13:1
7000 MHz	1.17:1
15000 MHz	1.25:1
20000 MHz	1.3:1

Table Notes: VSWR limit is a continuous sloping line from 500 MHz to 20 GHz

Attenuation

Frequency	Nom. Attenuation [dB/100ft]
500 MHz	15.0 dB/100ft
1000 MHz	22.5 dB/100ft
3000 MHz	32.8 dB/100ft
3000 MHz	41.2 dB/100ft
5000 MHz	54.9 dB/100ft
7000 MHz	66.4 dB/100ft
10000 MHz	81.2 dB/100ft

15000 MHz	102 dB/100ft
18000 MHz	113 dB/100ft
20000 MHz	120 dB/100ft

Power Rating

Frequency [MHz]	Max. Power Rating [W]
500 MHz	180 W
1,000 MHz	119 W
2,000 MHz	79 W
3,000 MHz	62 W
5,000 MHz	46 W
7,000 MHz	37 W
10,000 MHz	30 W
15,000 MHz	24 W
18,000 MHz	21 W
20,000 MHz	20 W

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedance	Nom. Velocity
64.2 Ohm/1000ft	10.2 Ohm/1000ft	29.5 pF/ft	50 Ohm	70%

Voltage

UL Voltage Rating	Non-UL Voltage Rating
30 V (UL AWM Style 10245)	1500 V

Mechanical Characteristics

Temperature

UL Rating	Operating
105°C	-70°C to +200°C

Bend Radius

Installation Min.
0.125 in

Bulk Cable Weight:	12 lbs/1000ft
Max. Pull Tension:	26 lbs

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Sustainability:	CA Prop 65
Flammability / Fire Resistance:	UL 1581 Horizontal Wire
AWM Compliance:	10245
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.357 Revision Date: 02-16-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.