



Product: [1829R](#)

Broadband Coax, Series 6, 18 AWG Solid BCCS, Foil + 60% AL Braid, PVC Jkt, CMP

Product Description

Broadband Coax, Series 6, 18 AWG Solid Bare Copper Covered Steel Conductor, PE Insulation, Foil + 60% Aluminum Braid Shield, PVC Jacket, CMR

Technical Specifications

Product Overview

Suitable Applications:	Broadband, Cable Television (CATV), RF drop cable, Direct Broadcast Satellite (DBS), Over-The-Air (OTA) antennas
------------------------	--

Construction Details

Series Type:	6
--------------	---

Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	18 AWG	Solid	0.04 in	BCCS - Bare Copper Covered Steel

Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene (Foam)	0.18 in (4.6 mm)	White

Table Notes:	Gas Injected
--------------	--------------

Outer Shield

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
2	Braid	Aluminum		60%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.275 in (6.99 mm)

Overall Cable Diameter (Nominal):	0.275 in (6.99 mm)
-----------------------------------	--------------------

Electrical Characteristics

Return Loss (RL)

Frequency	Min. Structural Return Loss
950 - 2250 MHz	15 dB
2250 - 3000 MHz	10 dB

Attenuation

Frequency	Nom. Attenuation	Max. Attenuation
5 MHz	0.5 dB/100ft	0.58 dB/100ft
55 MHz	1.4 dB/100ft	1.6 dB/100ft
211 MHz	2.6 dB/100ft	3.05 dB/100ft
500 MHz	4.1 dB/100ft	4.66 dB/100ft
750 MHz	5.1 dB/100ft	5.65 dB/100ft

862 MHz	5.5 dB/100ft	6.1 dB/100ft
1000 MHz	6 dB/100ft	6.55 dB/100ft
1450 MHz	7.8 dB/100ft	8 dB/100ft
1800 MHz	8.6 dB/100ft	8.8 dB/100ft
2250 MHz	9.8 dB/100ft	10 dB/100ft
3000 MHz	11.3 dB/100ft	11.9 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
28 Ohm/1000ft (92 Ohm/km)	9 Ohm/1000ft (30 Ohm/km)	16.2 pF/ft (53.1 pF/m)	75 Ohm	83%

Voltage

UL Voltage Rating
300 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation
75°C	-40°C To +80°C	-30°C To +80°C

Bend Radius

Stationary Min.	Installation Min.
2 in (51 mm)	2 in (51 mm)

Max. Pull Tension:	126 lbs (57.2 kg)
Bulk Cable Weight:	30 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Reaction to Fire:	UL 1666 Vertical Shaft, FT4
NEC / UL Compliance:	Article 800, CATVR, CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	1829A

Product Notes

Notes:	(1)RG Type :-In Stibo it was 6 But in BPCS only Series 6 is there. (2)# Elements@Conductor1:-In Stibo it was Blank and now changed to 1. (3)Size@Conductor1 :-In Stibo it was 18 now changed to 18AWG (4)Color@Color Chart1 01 :- In stibo it was Blank now Changed to White (5)Material@OuterShield1 1 - In stibo it is Tri-Laminate (Alum+Poly+Alum) But in BPCS (Heat fusible+ Alum+ Poly+Alum) (6)Coverage@OuterShield1 2 - in stibo it was 60% Now changed to 57% (7)Cable Diameter (Nominal)- In Stibo it was Blank Now Changed to 57% (8)Bulk Cable Weight - In stibo it was 29 lbs/1000 ft Now chnged to 30 lbs/1000 ft
--------	---

History

Update and Revision:	Revision Number: 0.469 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
1829R 010U1000	Black	UnReel	1,000 ft	612825124153
1829R 008U1000	Gray	UnReel	1,000 ft	612825124139
1829R 009U1000	White	UnReel	1,000 ft	612825124146

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.