


Product: [1675A](#) 

50 Ohm Microwave, RG401, 14 AWG SPC, Unjacketed



Product Description

50 Ohm, RG-401/U type, 14 AWG solid .065" silver-plated copper conductor, PTFE insulation, copper-tin composite shield (100% coverage), unjacketed.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
14	Solid	SCCS - Silvered Copper Covered Steel	0.065 in	1

Conductor Count:

Insulation

Material	Material Trade Name	Nominal Diameter
PTFE - Polytetrafluoroethylene	Teflon®	0.21 in

Outer Shield Material

Type	Layer	Material	Coverage [%]
Tape	1	Bare Copper (BC)	100%
Braid	2	Tinned Copper (TC + Tin Filled)	100%

Outer Jacket Material

Material
No Jacket

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
2.5 Ohm/1000ft	8 Ohm/1000ft	8 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
29.6 pF/ft

Inductance

Nominal Inductance
0.07 μ H/ft

Impedance

Nominal Characteristic Impedance
50 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
400 MHz	3.8 dB/100ft
500 MHz	4.4 dB/100ft

1000 MHz	6.8 dB/100ft
2000 MHz	10.4 dB/100ft
3000 MHz	13.4 dB/100ft
5000 MHz	18.5 dB/100ft
7000 MHz	22.8 dB/100ft
10000 MHz	28.4 dB/100ft
15000 MHz	36.6 dB/100ft
18000 MHz	41.0 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.46 ns/ft	70%

Power Rating

Frequency [MHz]	Max. Power Rating [W]	Nominal Power Rating [W]
400 MHz	1,900 W	1,900 W
500 MHz	1,665 W	1,665 W
1,000 MHz	1,105 W	1,105 W
2,000 MHz	733 W	733 W
3,000 MHz	577 W	577 W
5,000 MHz	427 W	427 W
7,000 MHz	350 W	350 W
10,000 MHz	283 W	283 W
15,000 MHz	223 W	223 W
18,000 MHz	200 W	200 W

Voltage

Non-UL Voltage Rating
2900 V RMS

VSWR

Element	Frequency [MHz]	Max. VSWR
Ramp Function, End Points	400 MHz	1.10:1
	1000 MHz	1.11:1
	3000 MHz	1.14:1
	7000 MHz	1.21:1
	10000 MHz	1.25:1
	18000 MHz	1.38:1

Electrical Characteristics Notes:	VSWR limit is a continuous sloping line from 500 MHz to 18 GHz
-----------------------------------	--

Temperature Range

Non-UL Temp Rating:	200°C
Operating Temp Range:	-70°C To +200°C

Mechanical Characteristics

Bulk Cable Weight:	81 lbs/1000ft
Max. Pull Tension:	122 lbs
Min Bend Radius During Installation:	0.375 in
Min Bend Radius During Operation:	1.125 in
Min Flexing Radius:	1.125 in

Standards

RG Type:	401/U Type
Qualified Products List (QPL):	No

Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes

EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
EU RoHS Compliance Date (yyyy-mm-dd):	2005-01-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
1675A TIN100	Tin	Reel	100 ft	612825120537
1675A TIN500	Tin	Reel	500 ft	612825120544

Footnote:	E - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'.
Footnote:	C - CRATE REEL PUT-UP.

Product Notes

Notes:	Commercial non-QPL product
--------	----------------------------

History

Update and Revision:	Revision Number: 0.344 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.