

Part Number: 1841AC

DBS Cable, Dual RG6, 18 AWG BCAC, Foil + Braid, CM



Product Description

Series 6, 18 AWG solid .040" bare copper-covered steel conductor, gas-injected foam polyethylene insulation, Duobond® II, Al. braid shield (60% coverage), PVC jacket.

Technical Specifications

Product Overview

| | |
|----------------------|------------------------------|
| Environmental Space: | Indoor (Not Riser or Plenum) |
|----------------------|------------------------------|

Physical Characteristics (Overall)

Conductor

| AWG | Stranding | Material | Nominal Diameter | No. of Coax |
|-----|-----------|---|------------------|-------------|
| 18 | Solid | BCAC - Bare Copper w/Anti-Corrosion Treatment | 0.0403 in | 2 |

| | |
|------------------------|----------------------|
| Conductor, Table Note: | Corrosion Resistance |
| Conductor Count: | 2 |
| Conductor Size: | 18 AWG |

Insulation

| Material | Nominal Diameter |
|--------------------------------------|------------------|
| Gas-injected FPE - Foam Polyethylene | 0.18 in |

Outer Shield Material

| Type | Layer | Material | Material Trade Name | Coverage [%] |
|-------|-------|-----------------------------|---------------------|--------------|
| Tape | 1 | Aluminum/Polyester/Aluminum | Bonded Duofoil® | 100 % |
| Braid | 2 | AL - Aluminum | | 60 % |

Outer Jacket Material

| Material | Nominal Diameter |
|--------------------------|------------------|
| PVC - Polyvinyl Chloride | .273 x .595 in |

Electrical Characteristics

Conductor DCR

| Nominal Conductor DCR | Nominal Outer Shield DCR | Outer Conductor DCR |
|-----------------------|--------------------------|---------------------|
| 6.4 Ohm/1000ft | 9 Ohm/1000ft | 9 Ohm/1000ft |

Capacitance

| Nom. Capacitance Conductor to Shield |
|--------------------------------------|
| 16.2 pF/ft |

Inductance

| Nominal Inductance |
|--------------------|
| 0.097 µH/ft |

Impedance

| Nominal Characteristic Impedance | Nominal Characteristic Tolerance |
|----------------------------------|----------------------------------|
| 75 Ohm | ± 3 Ohm |

Return Loss (RL)

| Frequency [MHz] | Min. Structural Return Loss (SRL) |
|-----------------|-----------------------------------|
| 950 - 2250 MHz | 15 dB |
| 2250 - 3000 MHz | 10 dB |

High Frequency (Nominal/Typical)

| Frequency [MHz] | Nom. Insertion Loss |
|-----------------|---------------------|
| 5 MHz | 0.5 dB/100ft |
| 55 MHz | 1.4 dB/100ft |
| 211 MHz | 2.6 dB/100ft |
| 500 MHz | 4.1 dB/100ft |
| 750 MHz | 5.1 dB/100ft |
| 862 MHz | 5.5 dB/100ft |
| 1000 MHz | 6 dB/100ft |
| 1450 MHz | 7.8 dB/100ft |
| 1800 MHz | 8.6 dB/100ft |
| 2250 MHz | 9.8 dB/100ft |
| 3000 MHz | 11.3 dB/100ft |

Delay

| Nominal Delay | Nominal Velocity of Propagation (VP) [%] |
|---------------|--|
| 1.2 ns/ft | 83 % |

High Freq

| Frequency [MHz] | Max. Insertion Loss (Attenuation) |
|-----------------|-----------------------------------|
| 5 MHz | 0.58 dB/100ft |
| 55 MHz | 1.6 dB/100ft |
| 211 MHz | 3.05 dB/100ft |
| 500 MHz | 4.66 dB/100ft |
| 750 MHz | 5.65 dB/100ft |
| 862 MHz | 6.1 dB/100ft |
| 1000 MHz | 6.55 dB/100ft |
| 1450 MHz | 8 dB/100ft |
| 1800 MHz | 8.8 dB/100ft |
| 2250 MHz | 10 dB/100ft |
| 3000 MHz | 11.9 dB/100ft |

Voltage

| Non-UL Voltage Rating |
|-----------------------|
| 300 V RMS |

Temperature Range

| | |
|-----------------------|----------------|
| Non-UL Temp Rating: | 80°C |
| Operating Temp Range: | -40°C To +80°C |

Mechanical Characteristics

| | |
|----------------------------------|---------------|
| Bulk Cable Weight: | 56 lbs/1000ft |
| Max Recommended Pulling Tension: | 252 lbs |
| Min Bend Radius/Minor Axis: | 3 in |

Standards

| | |
|--------------------------|----------|
| NEC/(UL) Specification: | CATV, CM |
| CEC/C(UL) Specification: | CM |
| RG Type: | 6/U Type |
| Series Type: | Series 6 |

Applicable Environmental and Other Programs

| | |
|------------------------------------|-----|
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2003/96/EC (BFR): | Yes |
| EU Directive 2011/65/EU (ROHS II): | Yes |
| EU Directive 2012/19/EU (WEEE): | Yes |

| | |
|---------------------------------------|-------------------------------|
| EU Directive 2015/863/EU: | Yes |
| EU Directive Compliance: | EU Directive 2003/11/EC (BFR) |
| EU CE Mark: | Yes |
| EU RoHS Compliance Date (yyyy-mm-dd): | 2004-01-01 |
| CA Prop 65 (CJ for Wire & Cable): | Yes |
| MII Order #39 (China RoHS): | Yes |

Suitability

| | |
|-----------------------|-----|
| Suitability - Indoor: | Yes |
|-----------------------|-----|

Flammability, LS0H, Toxicity Testing

| | |
|------------------|-------------------|
| UL Flammability: | UL1685 UL Loading |
|------------------|-------------------|

Plenum/Non-Plenum

| | |
|---------------|----|
| Plenum (Y/N): | No |
|---------------|----|

Part Number

Variants

| Item # | Color | Footnote |
|----------------|-------|----------|
| 1841AC 0101000 | Black | C |
| 1841AC 010500 | Black | C |
| 1841AC 008500 | Gray | C |
| 1841AC 009500 | White | C |

| | |
|-----------|------------------------|
| Footnote: | C - CRATE REEL PUT-UP. |
|-----------|------------------------|

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.