



Product: [1695A](#)

75 Ohm SDI Coax, RG-6, 18 AWG Solid BC, Foil + 95% TC Braid, PVC Jkt, CMP

Product Description

75 Ohm SDI Coax, RG-6, 18 AWG Solid Bare Copper Conductor, FEP Insulation, Foil + 95% Tinned Copper Braid Shield, PVC Jacket, CMP

Technical Specifications

Product Overview

Suitable Applications:	Digital Video, 6 Gb/s UHDTV, HD-SDI 1080p
------------------------	---

Construction Details

RG Type:	6
----------	---

Conductor

Size	Stranding	Nom. Diameter	Material
18 AWG	Solid	0.040 in	BC - Bare Copper

Insulation

Material	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene (Foam)	0.170 in (4.32 mm)	White

Outer Shield

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
2	Braid	Tinned Copper (TC)		95%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.229 in (5.82 mm)

Overall Cable Diameter (Nominal):	0.229 in (5.82 mm)
-----------------------------------	--------------------

Electrical Characteristics

Return Loss (RL)

Frequency	Min. Return Loss
5 - 1600 MHz	23 dB
1600 - 4500 MHz	21 dB
4500 - 6000 MHz	15 dB

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.24 dB/100ft
3.58 MHz	0.45 dB/100ft
5 MHz	0.55 dB/100ft
7 MHz	0.65 dB/100ft
10 MHz	0.75 dB/100ft
67.5 MHz	1.74 dB/100ft
71.5 MHz	1.78 dB/100ft

88.5 MHz	1.94 dB/100ft
100 MHz	2.1 dB/100ft
135 MHz	2.4 dB/100ft
143 MHz	2.5 dB/100ft
180 MHz	2.8 dB/100ft
270 MHz	3.4 dB/100ft
360 MHz	4.0 dB/100ft
540 MHz	5.2 dB/100ft
720 MHz	6.1 dB/100ft
750 MHz	6.2 dB/100ft
1000 MHz	7.4 dB/100ft
1500 MHz	9.5 dB/100ft
2000 MHz	11.3 dB/100ft
2250 MHz	12.2 dB/100ft
3000 MHz	14.6 dB/100ft
4500 MHz	18.6 dB/100ft
6000 MHz	22.4 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
6.4 Ohm/1000ft	2.8 Ohm/1000ft (9.2 Ohm/km)	16.2 pF/ft (53.1 pF/m)	75 Ohm	83%

Voltage

UL Voltage Rating
300 V (CMP)

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	0°C to +75°C

Bend Radius

Installation Min.
2.3 in (58 mm)

Max. Pull Tension:	92 lbs (42 kg)
Bulk Cable Weight:	41 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	NFPA 262
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	1694A

History

Update and Revision:	Revision Number: 0.570 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1695A 010500	Black	Reel	500 ft	612825121206	C
1695A 010Z500	Black	ReelTuff Box	500 ft	612825434603	
1695A 0101000	Black	Reel	1,000 ft	612825121190	C
1695A 010Z1000	Black	ReelTuff Box	1,000 ft	612825434504	
1695A 0105000	Black	Reel	5,000 ft	612825121213	C

1695A 01010000	Black	Reel	10,000 ft	612825435662	
1695A 006500	Blue, Light	Reel	500 ft	612825352938	
1695A 0061000	Blue, Light	Reel	1,000 ft	612825121169	C
1695A 006Z1000	Blue, Light	ReelTuff Box	1,000 ft	612825434474	
1695A 00610000	Blue, Light	Reel	10,000 ft	612825435716	
1695A 0011000	Brown	Reel	1,000 ft	612825121121	C
1695A 00110000	Brown	Reel	10,000 ft	612825435679	
1695A 0081000	Gray	Reel	1,000 ft	612825121183	C
1695A 00810000	Gray	Reel	10,000 ft	612825435747	
1695A N3U1000	Green, Mil	Reel	1,000 ft	612825121114	C
1695A N3U10000	Green, Mil	Reel	10,000 ft	612825435761	
1695A 877500	Natural	Reel	500 ft	612825121237	Z
1695A 8771000	Natural	Reel	1,000 ft	612825121220	C
1695A 877Z1000	Natural	ReelTuff Box	1,000 ft	612825434511	
1695A 87710000	Natural	Reel	10,000 ft	612825435754	
1695A 0031000	Orange	Reel	1,000 ft	612825121145	C
1695A 003Z1000	Orange	ReelTuff Box	1,000 ft	612825434450	
1695A 00310000	Orange	Reel	10,000 ft	612825435693	
1695A 0021000	Red	Reel	1,000 ft	612825121138	C
1695A 002Z1000	Red	ReelTuff Box	1,000 ft	612825434429	
1695A 00210000	Red	Reel	10,000 ft	612825435686	
1695A 0071000	Violet	Reel	1,000 ft	612825121176	C
1695A 007Z1000	Violet	ReelTuff Box	1,000 ft	612825434481	
1695A 0075000	Violet	Reel	5,000 ft	612825353195	
1695A 00710000	Violet	Reel	10,000 ft	612825435730	
1695A 0041000	Yellow	Reel	1,000 ft	612825121152	C
1695A 004Z1000	Yellow	ReelTuff Box	1,000 ft	612825434467	
1695A 00410000	Yellow	Reel	10,000 ft	612825435709	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.