



**Product:** [1855ENH](#)

1855ENH - 75 Ohm SDI Coax, Mini RG-59, 22 AWG Solid BC, Foil + 90% TC Braid, LSZH Jkt

## Product Description

75 Ohm SDI Coax, Mini RG-59, 22 AWG Solid Bare Copper Conductor, PE Insulation, Foil + 90% Tinned Copper Braid Shield, LSZH Jacket, Dca. IEC 60332-1-2.

## Technical Specifications

### Product Overview

Suitable Applications:	Digital Video, 6 Gb/s UHD TV, HD-SDI 1080p; Cable is UV-resistant and suitable for indoor and outdoor use
------------------------	---

### Construction Details

RG Type:	Mini 59
----------	---------

#### Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	22 AWG	Solid	0.65 mm	BC - Bare Copper

#### Insulation

Element	Material	Nom. Insulation Diameter
Insulated Conductor	PE - Polyethylene (Foam)	2.9 mm (0.11 in)

#### Outer Shield

Layer	Outer Shield Type	Material	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	100%
2	Braid	Tinned Copper (TC)	90%

#### Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	4.45 mm

Table Notes:	According to EN 50290-2-20
--------------	----------------------------

## Electrical Characteristics

#### Attenuation

Frequency	Nom. Attenuation
1 MHz	1.7 dB/100m
3.6 MHz	2.5 dB/100m
5 MHz	2.8 dB/100m
6 MHz	3 dB/100m
7 MHz	3.2 dB/100m
10 MHz	3.7 dB/100m
12 MHz	4 dB/100m
25 MHz	5.4 dB/100m
67.5 MHz	8.3 dB/100m
71.5 MHz	8.6 dB/100m
88.5 MHz	9.5 dB/100m
100 MHz	10 dB/100m

135 MHz	11.5 dB/100m
143 MHz	11.9 dB/100m
180 MHz	13.2 dB/100m
270 MHz	16.1 dB/100m
360 MHz	18.6 dB/100m
540 MHz	22.8 dB/100m
720 MHz	26.4 dB/100m
750 MHz	26.9 dB/100m
1000 MHz	31.3 dB/100
1500 MHz	38.7 dB/100m
2000 MHz	45 dB/100m
2250 MHz	48 dB/100m
2500 MHz	50.8 dB/100m
3000 MHz	56.1 dB/100m
4000 MHz	65.7 dB/100m
4500 MHz	70.2 dB/100m

#### Electricals

Max. Conductor DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
55 Ohm/km (17 Ohm/1000ft)	53 pF/m (16 pF/ft)	75 Ohm	84%

#### Transfer Impedance

Frequency	Max. Transfer Impedance
5-30 MHz	Max. 15 mOhm/m

#### Screening

Frequency	Min. Screening Attenuation
30 - 1000 MHz	85 dB
1000 - 2000 MHz	
2000 - 3000 MHz	
3000 - 4500 MHz	

Screening Class: B

#### Voltage

Voltage Rating
75 V DC

## Mechanical Characteristics

#### Temperature

Operating	Installation	Storage
-30°C To +70°C	-5°C To +50°C	-30°C To +70°C

#### Bend Radius

Stationary Min.
45 mm (1.8 in)

Max. Pull Tension: 160 N (36 lbf)

## Standards and Compliance

Environmental Suitability:	Indoor/Outdoor - Euroclass Dca
Flammability / Reaction to Fire:	IEC 60332-1-2, CEI 20-35/1
CPR Compliance:	CPR Euroclass: Dca-s1,d1,a1; CPR UKCA Class: Dca-s1,d1,a1
ISO/IEC Compliance:	IEC 61034-2 - Smoke Density Min Transmittance = 60%
GENELEC Compliance:	EN 50117-1, EN 50290-2-20
European Halogen Free Standards:	IEC 62821-1 Halogen Free Compliance = Yes, IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 2.5 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

## History

Update and Revision: Revision Number: 0.298 Revision Date: 02-28-2025

### Variants

Item #	Color	Putup Type	Length	EAN
1855ENH.08500	Black	Reel	500 m	8719605004352
1855ENH.17100	Blue	Reel	100 m	8719605004437
1855ENH.07500	Blue	Reel	500 m	8719605004345
1855ENH.071000	Blue	Reel	1,000 m	8719605004338
1855ENH.03500	Cream	Reel	500 m	8719605004277
1855ENH.10100	Green	Reel	100 m	8719605004383
1855ENH.00500	Green	Reel	500 m	8719605004222
1855ENH.001000	Green	Reel	1,000 m	8719605004185
1855ENH.002000	Green	Reel	2,000 m	8719605004192
1855ENH.06500	Orange	Reel	500 m	8719605004321
1855ENH.05500	Violet	Reel	500 m	8719605004314
1855ENH.051000	Violet	Reel	1,000 m	8719605004291
1855ENH.01500	White	Reel	500 m	8719605004246
1855ENH.09500	Yellow	Reel	500 m	8719605004376

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.