


Product: [1862A](#) 

Speaker Cable, 2 Conductor 16 AWG BC, Unshielded, CMP



Product Description

Speaker Cable, 2 Conductor 16 AWG stranded (19x29) high conductivity bare copper conductors with Flamarrest® insulation, cabled in an open twisted construction, Plenum-CL3P.

Technical Specifications

Product Overview

Suitable Applications:	Speaker Cable
------------------------	---------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
16	19x29	BC - Bare Copper	2

Conductor Count:	2
------------------	---

Insulation

Material	Material Trade Name	Nominal Wall Thickness
PVC - Polyvinyl Chloride	Flamarrest®	0.022 in

Outer Shield Material

Material
No Shield

Outer Jacket Material

Nominal Diameter
0.202 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
4.2 Ohm/1000ft

Inductance

Nominal Inductance
0.186 µH/ft

Current

Max. Recommended Current [A]
6.5 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
150 V RMS

Temperature Range

Non-UL Temp Rating:	75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	24 lbs/1000ft
Max. Pull Tension:	60.8 lbs
Min Bend Radius/Minor Axis:	2.25 in

Standards

NEC/(UL) Compliance:	CL3P
----------------------	------

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Plenum
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262
UL voltage rating:	150 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
1862A D261000	Black & Natural Pair	Reel	1,000 ft	612825125167

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.265 Revision Date: 06-24-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.