



REPRESENTATIVE IMAGE

Product: [1800B](#)

Digital Audio Cable, 1 Pr #24 Str TC, O/A Foil, PVC Jkt, CMR

Product Description

Digital Audio Cable, 1 Pair 24 AWG (7 x 32) Tinned Copper, Datalene® Insulation, Overall Beldfoil® Shield, PVC Jacket, CMR

Technical Specifications

Product Overview

Suitable Applications:	Digital audio, Interconnect between audio equipment such as microphones, speakers, amplifiers, mixing consoles
------------------------	--

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	1	24 AWG	7x32	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code	Notes
Pair(s)	PE - Polyethylene (Foam)	0.022 in (0.56 mm)	0.068 in (1.7 mm)	Red & Black	HDPE

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.023 in (0.58 mm)	0.185 in (4.70 mm)

Table Notes:	Jacket and shield are bonded so both can be removed with automatic stripping equipment.
Cable Diameter (Nominal):	0.185 in (4.70 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Pair(s)	23.7 Ohm/1000ft (77.8 Ohm/km)	12 pF/ft (39 pF/m)	26 pF/ft (85 pF/m)	110 Ohm	76%	2.75 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V (CMR)

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C	-30°C to +60°C

Bend Radius

Stationary Min.	Installation Min.

1.9 in (48 mm)	1.9 in (48 mm)
----------------	----------------

Max. Pull Tension:	16.5 lbs (7.48 kg)
Bulk Cable Weight:	16 lbs/1000ft (24 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMR
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	AES/EBU
Plenum Number:	1801B

Product Notes

Notes:	For cross-connect use with 1803F (et al.) Digital Audio Snake Cables.
--------	---

History

Update and Revision:	Revision Number: 0.359 Revision Date: 10-13-2021
----------------------	--

Variants

Item #	Color	Putup Type	Length	UPC
1800B T5X5000	Gray	Reel	5,000 ft	612825427995
1800B T5X500	Gray T5X	Reel	500 ft	612825122791
1800B T5X1000	Gray T5X	Reel	1,000 ft	612825122784
1800B T5XU1000	Gray T5X	UnReel	1,000 ft	612825122777
1800B 0071000	Violet	Reel	1,000 ft	612825122814
1800B 007U1000	Violet	UnReel	1,000 ft	612825122807
1800B 0075000	Violet	Reel	5,000 ft	612825427988

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.