




**Product:** [1808A](#)



S-Video, High-Flex, Dual Mini 75 Ohm #30 Coax, Round

## Product Description

S-Video Cable, 2-30 AWG stranded tinned copper coax, foam HDPE insulation, 90% tinned copper spiral serve shield, PVC jacket

## Technical Specifications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
30	7x38	TC - Tinned Copper	0.013 in	2

Conductor Count:	2
------------------	---

#### Insulation

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.058 in

#### Color Chart

Number	Color
1	Black
2	Yellow

#### Inner Shield

Type	Material	Coverage [%]
Spiral Serve / Screen	Tinned Copper (TC)	90%

#### Inner Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.1 in

#### Outer Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.254 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Inner Shield DCR	Outer Conductor DCR
100 Ohm/1000ft	100 Ohm/1000ft	7.5 Ohm/1000ft	7.5 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Shield
17.3 pF/ft

#### Inductance

Nominal Inductance
0.097 $\mu$ H/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.6 dB/100ft
5 MHz	1.4 dB/100ft
10 MHz	2.1 dB/100ft
30 MHz	3.8 dB/100ft
50 MHz	5.1 dB/100ft
100 MHz	7.6 dB/100ft
200 MHz	11.3 dB/100ft
400 MHz	16.9 dB/100ft
700 MHz	23.3 dB/100ft
900 MHz	26.9 dB/100ft
1000 MHz	28.6 dB/100ft

Delay

Nominal Velocity of Propagation (VP) [%]
78%

Voltage

Non-UL Voltage Rating	UL Voltage Rating
300 V RMS	30 V RMS

Temperature Range

Non-UL Temp Rating:	75°C
UL Temp Rating:	60°C
Operating Temperature Range:	-40°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	29 lbs/1000ft
Max. Pull Tension:	12 lbs
Min. Bend Radius/Minor Axis:	2.5 in

Standards

UL AWM Style Compliance:	AWM 1354
RG Type:	Ultra-miniature 59

Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Flammability, LS0H, Toxicity Testing

UL voltage rating:	30 V RMS
--------------------	----------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
1808A B59500	Black, Matte	Reel	500 ft	612825357100
1808A B59U500	Black, Matte	UnReel	500 ft	612825357124
1808A B591000	Black, Matte	Reel	1,000 ft	612825357117
1808A B59U1000	Black, Matte	UnReel	1,000 ft	612825357131

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	Inner Jacket Separator Material: Paper Tape.
--------	--

History

Update and Revision:	Revision Number: 0.336 Revision Date: 04-29-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.