




Product: [1811A](#)



Speaker Cable, 8 Conductor 14 AWG BC, Unshielded, PVC Jkt

Product Description

Speaker Cable, 8 Conductor 14 AWG stranded (104x34) bare copper conductors with PVC insulation, cabled with fillers, paper wrap, flexible PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Bi-amp & Tri-amp Spkr Conn
------------------------	----------------------------

Construction Details

Conductor

Size	Stranding	Material
14	104x34	BC - Bare Copper

Insulation

Material	Nom. Thickness	Color Code
PVC - Polyvinyl Chloride	0.025 in (0.64 mm)	Brown, Red, Orange, Yellow, Green, White, Blue, Black

Outer Shield

Material
No Shield

Outer Jacket

Separator	Material	Nom. Thickness	Nom. Diameter
Paper Tape	PVC - Polyvinyl Chloride	0.04 in (1.0 mm)	0.515 in (13.1 mm)

Electrical Characteristics

Electricals

Nom. Conductor DCR	Max. Current
2.7 Ohm/1000ft	9.5 Amps per Conductor at 25°C

Voltage

Voltage Rating
300 V

Mechanical Characteristics

Temperature

Operating
-20°C To +60°C

Max. Pull Tension:	400 lbs (180 kg)
Bulk Cable Weight:	189 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
----------------------------	--------------------------------------

European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Suggested Connectors: Neutrik Speakon®.
--------	---

History

Update and Revision:	Revision Number: 0.417 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1811A B591000	Black, Matte	Reel	1,000 ft	612825123330	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.