



Product: [1813A](#)

Audio Cable, 2 Conductor 24 AWG, BC



Product Description

Audio Cable, CM-Rated, 1-24 AWG stranded high-conductivity bare copper pair with PVC insulation, +90% bare copper spiral shield, PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Multi-channel interconnect between audio equipment such as microphones, speakers, amplifiers, mixing consoles; Live events or studio sound; Analog audio
------------------------	--

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	2	24 AWG	27x38	BC - Bare Copper (High Conductivity)

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.059 in mm	Blue, Red

Outer Shield

Shield Type	Material	Coverage
Spiral Serve / Screen	Bare Copper (BC)	90%

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.055 in (1.4 mm)	0.236 in

Overall Cable Diameter (Nominal): 0.236 in

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
22.8 Ohm/1000ft	33 pF/ft (110 pF/m)	61 pF/ft (200 pF/m)	3.9 Amps per Conductor at 25°C

Voltage

Voltage Rating
30 V

Mechanical Characteristics

Temperature

Operating
-30°C To +60°C

Bend Radius

Stationary Min.	Installation Min.
7.25 in (184 mm)	7.25 in

Max. Pull Tension: 10 lbs (4.5 kg)

Bulk Cable Weight:	30 lbs/1000ft
--------------------	---------------

Standards and Compliance

European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.455 Revision Date: 01-20-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
1813A B59328	Black, Matte	Reel	328 ft	612825123408
1813A B591000	Black, Matte	Reel	1,000 ft	612825123392

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.