



**Part Number:** 19106

Portable Cordage, 3 C #12 Str BC, EPDM Ins, Rubber Jkt, UL Type S

[Request Sample](#)

**Product Description**

Portable Cordage, 3 Conductor 12AWG (65x30) Bare Copper, EPDM Insulation, Rubber Outer Jacket, UL Type S

**Technical Specifications**

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Conductors
12	65x30	BC - Bare Copper	3

Conductor Count: 3

**Insulation**

Material	Nominal Wall Thickness
EPDM - Ethylene Propylene Diene Monomer Rubber	0.051 in

**Color Chart**

Color
Black
White
Green

**Outer Shield Material**

Material
Unshielded

**Outer Jacket Material**

Material	Nominal Diameter	Nominal Wall Thickness	Separator Material
Rubber	0.64 in	0.099 in	Paper Tape

**Construction and Dimensions**

Type of Cordage: S

**Cabling**

Filler
Jute

**Electrical Characteristics**

**Current**

Max. Recommended Current [A]
25 Amps per conductor @ 25°C; 18 Amps per conductor @ 25 °C over 50 ft.
18 Amps per conductor @ 25°C over 50 ft.

**Voltage**

Dielectric Withstand Voltage	UL Voltage Rating
3000 V AC Applied For 1 Min.	600 V RMS

Electrical Characteristics Notes:	3000 V AC Applied For 1 Min.
-----------------------------------	------------------------------

## Temperature Range

UL Temp Rating:	60°C
-----------------	------

## Mechanical Characteristics

Bulk Cable Weight:	227 lbs/1000ft
Min Bend Radius/Minor Axis:	6.5 in

## Standards

NEC/(UL) Specification:	S
CSA AWM Specification:	S

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-10-13
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Flammability, LSOH, Toxicity Testing

CSA Flammability:	FT2
UL voltage rating:	600 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	UPC	Length	Footnote
19106 010250	Black	612825126485	250 ft	C F

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Footnote:	F - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'.
-----------	--

## Product Notes

Notes:	Cabling Paper Separator Tape
--------	------------------------------

## History

Update and Revision:	Revision Number: 0.299 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.