



**Product:** [19126](#)

Portable Cordage, 2 C #16 Str BC, PVC Ins, UL Type SPT-2

[Request Sample](#)

**Product Description**

Portable Cordage, 2 Conductor 16AWG (65x34) Bare Copper, PVC Insulation, UL Type SPT-2

**Technical Specifications**

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Conductors
16	65x34	BC - Bare Copper	2

Conductor Count: 2

**Insulation**

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.048 in

**Outer Shield Material**

Material
No Shield

**Outer Jacket Material**

Nominal Diameter
0.155 x 0.299 in

**Construction and Dimensions**

Type of Cordage: SPT-2

**Electrical Characteristics**

**Current**

Max. Recommended Current [A]
13 Amps per Conductor at 25°C (10 Amps over 50 ft)
10 Amps per Conductor at 25°C (over 50 ft)

**Voltage**

Dielectric Withstand Voltage	UL Voltage Rating
1500 V AC Applied for 1 Min.	300 V RMS

Electrical Characteristics Notes: Dielectric Withstand Voltage: 1500 V AC Applied for 1 Min

**Temperature Range**

UL Temp Rating: 60°C

**Mechanical Characteristics**

Bulk Cable Weight:	35 lbs/1000ft
Min Bend Radius/Minor Axis:	1.75 in

## Standards

NEC/(UL) Compliance:	SPT-2
CSA AWM Compliance:	SPT-2

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

## Flammability, LSOH, Toxicity Testing

CSA Flammability:	FT2
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
19126 010250	Black	Reel	250 ft	612825126669

Footnote: F - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'.

## History

Update and Revision:	Revision Number: 0.298 Revision Date: 02-16-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.