



**Product:** [19130](#)

Portable Cordage, 3 C #16 Str BC, EPDM Ins, Rubber Jkt, UL Type SJ

[Request Sample](#)

**Product Description**

Portable Cordage, 3 Conductor 16AWG (26x30) Bare Copper, EPDM Insulation, Rubber Outer Jacket, UL Type SJ

**Technical Specifications**

**Construction Details**

**Conductor**

Element	Number of Element	Size	Stranding	Material
Conductor(s)	3	16 AWG	26x30	BC - Bare Copper

**Insulation**

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	EPDM - Ethylene Propylene Diene Monomer	0.031 in (0.79 mm)	0.123 in mm	Black, White, Green

**Outer Shield**

Material
No Shield

**Outer Jacket**

Separator	Material	Nom. Thickness	Nom. Diameter
Paper Tape	SBR - Styrene Butadiene Rubber	0.044 in (1.1 mm)	0.353 in

Overall Cable Diameter (Nominal):	0.353 in
-----------------------------------	----------

**Electrical Characteristics**

**Electricals**

Nom. Conductor DCR	Max. Current
4.4 Ohm/1000ft	19 Amps per Conductor at 25°C (10 Amps over 50 ft)
	10 Amps per Conductor at 25°C (over 50 ft)

**Voltage**

UL Voltage Rating
300 V

**Mechanical Characteristics**

**Temperature**

UL Temperature	Operating
60°C	-25°C to 60°C

**Bend Radius**

Stationary Min.	Installation Min.
3.53 in (89.7 mm)	3.53 in

Max. Pull Tension:	80 lbs (36 kg)
Bulk Cable Weight:	70 lbs/1000ft

## Standards and Compliance

Flammability / Reaction to Fire:	FT2, FT2
NEC / UL Compliance:	Article 400, SJ
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## Product Notes

Notes:	Cabling Paper Separator Tape
--------	------------------------------

## History

Update and Revision:	Revision Number: 0.385 Revision Date: 04-08-2022
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC
19130 010250	Black	Reel	250 ft	612825126683

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.