




Product: [1839A](#)



DBS Cable, RG6, 18 AWG BCCS, Foil + Braid, Messenger

Product Description

Series 6, 18 AWG solid .040" bare copper-covered steel conductor, gas-injected foam polyethylene insulation, Duobond® II, Al. braid shield (60% coverage), .045" bare copper-covered steel static ground, PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

| AWG | Stranding | Material | Nominal Diameter | No. of Coax |
|-----|-----------|----------------------------------|------------------|-------------|
| 18 | Solid | BCCS - Bare Copper Covered Steel | 0.04 in | 1 |

| | |
|------------------|---|
| Conductor Count: | 1 |
|------------------|---|

Insulation

| Material | Nominal Diameter |
|--------------------------|------------------|
| PE - Polyethylene (Foam) | 0.18 in |

| | |
|--------------|--------------|
| Table Notes: | Gas Injected |
|--------------|--------------|

Outer Shield

| Type | Layer | Material | Material Trade Name | Coverage [%] |
|-------|-------|-------------------------------|---------------------|--------------|
| Tape | 1 | Tri-Laminate (Alum+Poly+Alum) | Duofoil® | 100% |
| Braid | 2 | Aluminum | | 60% |

Outer Jacket

| Material | Nominal Diameter |
|--------------------------|------------------|
| PVC - Polyvinyl Chloride | 0.27 x 0.405 in |

Construction and Dimensions

| | |
|-------------------------|----------------------------------|
| Static Ground: | BCCS - Bare Copper Covered Steel |
| Static Ground Diameter: | 0.045 in |

Electrical Characteristics

Conductor DCR

| Nominal Conductor DCR | Nominal Outer Shield DCR | Outer Conductor DCR |
|-----------------------|--------------------------|---------------------|
| 28 Ohm/1000ft | 9 Ohm/1000ft | 9 Ohm/1000ft |

Capacitance

| Nom. Capacitance Conductor to Shield |
|--------------------------------------|
| 16.2 pF/ft |

Inductance

| Nominal Inductance |
|--------------------|
| 0.097 µH/ft |

Impedance

| Nominal Characteristic Impedance |
|----------------------------------|
|----------------------------------|

75 Ohm

Return Loss (RL)

| Frequency [MHz] | Min. Structural Return Loss (SRL) |
|-----------------|-----------------------------------|
| 950 - 2250 MHz | 15 dB |
| 2250 - 3000 MHz | 10 dB |

High Frequency (Nominal/Typical)

| Frequency [MHz] | Nom. Insertion Loss |
|-----------------|---------------------|
| 5 MHz | 0.5 dB/100ft |
| 55 MHz | 1.4 dB/100ft |
| 211 MHz | 2.6 dB/100ft |
| 500 MHz | 4.1 dB/100ft |
| 750 MHz | 5.1 dB/100ft |
| 862 MHz | 5.5 dB/100ft |
| 1000 MHz | 6 dB/100ft |
| 1450 MHz | 7.8 dB/100ft |
| 1800 MHz | 8.6 dB/100ft |
| 2250 MHz | 9.8 dB/100ft |
| 3000 MHz | 11.3 dB/100ft |

Delay

| Nominal Delay | Nominal Velocity of Propagation (VP) [%] |
|---------------|--|
| 1.2 ns/ft | 83% |

High Frequency

| Frequency [MHz] | Max. Insertion Loss (Attenuation) |
|-----------------|-----------------------------------|
| 5 MHz | 0.58 dB/100ft |
| 55 MHz | 1.6 dB/100ft |
| 211 MHz | 3.05 dB/100ft |
| 500 MHz | 4.66 dB/100ft |
| 750 MHz | 5.65 dB/100ft |
| 862 MHz | 6.1 dB/100ft |
| 1000 MHz | 6.55 dB/100ft |
| 1450 MHz | 8 dB/100ft |
| 1800 MHz | 8.8 dB/100ft |
| 2250 MHz | 10 dB/100ft |
| 3000 MHz | 11.9 dB/100ft |

Voltage

| Non-UL Voltage Rating |
|-----------------------|
| 350 V RMS |

Temperature Range

| | |
|------------------------------|----------------|
| Non-UL Temp Rating: | 80°C |
| Operating Temperature Range: | -40°C To +80°C |

Mechanical Characteristics

| | |
|------------------------------|---------------|
| Bulk Cable Weight: | 41 lbs/1000ft |
| Max. Pull Tension: | 160 lbs |
| Min. Bend Radius/Minor Axis: | 3 in |

Standards

| | |
|--------------|---|
| RG Type: | 6 |
| Series Type: | 6 |

Applicable Environmental and Other Programs

| | |
|-----------------------------------|------------------------------|
| Environmental Space: | Indoor (Not Riser or Plenum) |
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2003/96/EC (BFR): | Yes |
| EU Directive 2011/65/EU (RoHS 2): | Yes |

| | |
|--|-------------------------------|
| EU Directive 2012/19/EU (WEEE): | Yes |
| EU Directive 2015/863/EU (RoHS 2 amendment): | Yes |
| EU Directive Compliance: | EU Directive 2003/11/EC (BFR) |
| EU CE Mark: | No |
| MII Order #39 (China RoHS): | Yes |

Suitability

| | |
|-----------------------|-----|
| Suitability - Indoor: | Yes |
|-----------------------|-----|

Plenum/Non-Plenum

| | |
|---------------|----|
| Plenum (Y/N): | No |
|---------------|----|

Related Part Numbers

Variants

| Item # | Color | Put-Up Type | Length | UPC |
|---------------|-------|-------------|----------|--------------|
| 1839A 0101000 | Black | Reel | 1,000 ft | 612825124276 |

| | |
|-----------|------------------------|
| Footnote: | C - CRATE REEL PUT-UP. |
|-----------|------------------------|

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.385 Revision Date: 04-29-2024 |
|----------------------|--|

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.