



Product: [1841A](#)



DBS Cable, Dual RG6, 18 AWG BCCS, Foil + Braid, CM

## Product Description

Series 6 (RG6/U type Dual Coax), 18 AWG solid .040" bare copper-covered steel conductor, gas-injected foam polyethylene insulation, Duobond® II, Al. braid shield (60% coverage), PVC jacket.

## Technical Specifications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
18	Solid	BCCS - Bare Copper Covered Steel	0.04 in	2

Conductor Count:	2
------------------	---

#### Insulation

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.18 in

Table Notes:	Gas Injected
--------------	--------------

#### Outer Shield

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Aluminum		60%

#### Outer Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.273 x 0.595 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
28 Ohm/1000ft	9 Ohm/1000ft	9 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Shield
16.2 pF/ft

#### Inductance

Nominal Inductance
0.097 µH/ft

#### Impedance

Nominal Characteristic Impedance
75 Ohm

#### Return Loss (RL)

Frequency [MHz]	Min. Structural Return Loss (SRL)
-----------------	-----------------------------------

950 - 2250 MHz	15 dB
2250 - 3000 MHz	10 dB

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
5 MHz	0.5 dB/100ft
55 MHz	1.4 dB/100ft
211 MHz	2.6 dB/100ft
500 MHz	4.1 dB/100ft
750 MHz	5.1 dB/100ft
862 MHz	5.5 dB/100ft
1000 MHz	6 dB/100ft
1450 MHz	7.8 dB/100ft
1800 MHz	8.6 dB/100ft
2250 MHz	9.8 dB/100ft
3000 MHz	11.3 dB/100ft

#### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.2 ns/ft	83%

#### High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)
5 MHz	0.58 dB/100ft
55 MHz	1.6 dB/100ft
211 MHz	3.05 dB/100ft
500 MHz	4.66 dB/100ft
750 MHz	5.65 dB/100ft
862 MHz	6.1 dB/100ft
1000 MHz	6.55 dB/100ft
1450 MHz	8 dB/100ft
1800 MHz	8.8 dB/100ft
2250 MHz	10 dB/100ft
3000 MHz	11.9 dB/100ft

#### Voltage

Non-UL Voltage Rating
350 V RMS

#### Temperature Range

Non-UL Temp Rating:	80°C
Operating Temperature Range:	-40°C To +80°C

#### Mechanical Characteristics

Bulk Cable Weight:	56 lbs/1000ft
Max. Pull Tension:	252 lbs
Min. Bend Radius/Minor Axis:	3 in

#### Standards

NEC/(UL) Compliance:	CATV, CM
CEC/C(UL) Compliance:	CM
CPR Euroclass:	Eca
RG Type:	6
Series Type:	6

#### Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes

EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
MII Order #39 (China RoHS):	Yes

### Suitability

Suitability - Indoor:	Yes
-----------------------	-----

### Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
------------------	-------------------

### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

### Related Part Numbers

#### Variants

Item #	Color	Put-Up Type	Length	UPC
1841A 0101000	Black	Reel	1,000 ft	612825124351

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

### History

Update and Revision:	Revision Number: 0.432 Revision Date: 04-29-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.