



Product: [19404](#)

Portable Cordage, (2) 16 AWG (105x36) BC, CPE, Type HPN

[Request Sample](#)

Product Description

Two 16 AWG stranded (105x36) bare copper conductors, CPE insulation.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
16	105x36	BC - Bare Copper	2

Conductor Count:	2
------------------	---

Insulation

Material	Nominal Wall Thickness
CPE - Chlorinated Polyethylene	0.043 in

Outer Shield

Material
No Shield

Outer Jacket

Nominal Diameter
0.152 x 0.3 in

Construction and Dimensions

Type of Cordage:	HPN
------------------	-----

Electrical Characteristics

Current

Max. Recommended Current [A]
15 Amps per Conductor at 25°C (12 Amps over 50 ft)
15 Amps per Conductor at 25°C

Voltage

Dielectric Withstand Voltage	UL Voltage Rating
1500 V AC Applied For 1 Min.	300 V RMS

Electrical Characteristics Notes:	Dielectric Withstand Voltage: 1500 V AC Applied For 1 Min
-----------------------------------	---

Mechanical Characteristics

Bulk Cable Weight:	36 lbs/1000ft
Min. Bend Radius/Minor Axis:	1.75 in

Standards

NEC/(UL) Compliance:	HPN
CSA AWM Compliance:	HPN

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	VW-1
CSA Flammability:	FT2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

History

Update and Revision:	Revision Number: 0.186 Revision Date: 04-08-2022
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.