




Product: [1855DNH](#)

1855DNH - 75 Ohm SDI Coax, Mini RG-59, 22 AWG Solid BC, Tri-Shield, LSZH-C Jkt



Product Description

75 Ohm SDI Coax, Mini RG-59, 22 AWG Solid Bare Copper Conductor, PE Insulation, Foil + 90% Tinned Copper Braid + Foil Shield, LSZH Jacket, Dca. IEC 60332-3-24.

Technical Specifications

Product Overview

Suitable Applications:	Digital Video, 6 Gb/s UHD TV, HD-SDI 1080p; The outer conductor is designed for high screening attenuation and low transfer impedance; The cable is UV-resistant and suitable for indoor and outdoor use
------------------------	--

Construction Details

RG Type:	Mini 59
----------	---------

Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	22 AWG	Solid	0.65 mm	BC - Bare Copper

Insulation

Element	Material	Nom. Insulation Diameter
Insulated Conductor	PE - Polyethylene (Foam)	2.9 mm (0.11 in)

Outer Shield

Layer	Outer Shield Type	Material	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	100%
2	Braid	Tinned Copper (TC)	80%
3	Tape	Bi-Laminate (Alum+Poly)	100%

Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	4.45 mm

Table Notes:	According to EN 50290-2-20
--------------	----------------------------

Electrical Characteristics

Return Loss (RL)

Frequency	Min. Return Loss
5 - 1600 MHz	23 dB
1600 - 4500 MHz	21 dB

Attenuation

Frequency	Nom. Attenuation
1 MHz	1.7 dB/100m
3.6 MHz	2.5 dB/100m
5 MHz	2.8 dB/100m
6 MHz	3 dB/100m
7 MHz	3.2 dB/100m
10 MHz	3.7 dB/100m

12 MHz	4 dB/100m
25 MHz	5.4 dB/100m
67.5 MHz	8.3 dB/100m
71.5 MHz	8.6 dB/100m
88.5 MHz	9.5 dB/100m
100 MHz	10 dB/100m
135 MHz	11.5 dB/100m
143 MHz	11.9 dB/100m
180 MHz	13.2 dB/100m
270 MHz	16.1 dB/100m
360 MHz	18.6 dB/100m
540 MHz	22.8 dB/100m
720 MHz	26.4 dB/100m
750 MHz	26.9 dB/100m
1000 MHz	31.3 dB/100m
1500 MHz	38.7 dB/100m
2000 MHz	45 dB/100m
2250 MHz	48 dB/100m
2500 MHz	50.8 dB/100m
3000 MHz	56.1 dB/100m
4000 MHz	65.7 dB/100m
4500 MHz	70.2 dB/100m

Electricals

Max. Conductor DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
55 Ohm/km (17 Ohm/1000ft)	53 pF/m (16 pF/ft)	75 Ohm	84%

Transfer Impedance

Max. Transfer Impedance
Max. 5 mOhm/m

Screening

Frequency	Min. Screening Attenuation
30 - 1000 MHz	85 dB
1000 - 2000 MHz	
2000 - 3000 MHz	
3000 - 4500 MHz	

Screening Class: A

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-30°C To +70°C	-5°C To +50°C	-30°C To +70°C

Max. Pull Tension: 160 N (36 lbf)

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor - Euroclass Dca
Flammability / Reaction to Fire:	IEC 60332-1-2, IEC 60332-3-24, CEI 20-22-3
CPR Compliance:	CPR Euroclass: Dca-s2,d1,a1
CENELEC Compliance:	EN 50117-1
European Halogen Free Standards:	IEC 62821-1 Halogen Free Compliance = Yes, IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 2.5 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

History

Update and Revision: Revision Number: 0.285 Revision Date: 02-28-2025

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
1855DNH.02500	Gray	Reel	500 m	8719605004109
1855DNH.00500	Violet	Reel	500 m	8719605004086

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.