



Part Number: 1875GB

CAT6+ Patch Bonded-Pair, 4pr, UTP, PVC Jkt, CMR

Product Description

CAT6+ (350MHz), 4-Bonded-pairs, U/UTP-unshielded, Riser-CMR, Premise Patch cable, 24 AWG Bonded stranded (7x32) tinned copper conductor, polyolefin insulation, PVC jacket

Technical Specifications

Product Overview

Environmental Space:	Riser
Suitable Applications:	Premise Patch Cable Designed for Attenuation Stability in High Humidity Environments, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments, For T568-B Wiring

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	7x32	TC - Tinned Copper, Bonded Strands	4

Conductor Count:	8
Total Number of Pairs:	4

Insulation

Material	
PO - Polyolefin	
Bonded-Pair:	Yes

Color Chart

Number	Color
1	White/Brown Stripe & Brown
2	White/Blue Stripe & Blue
3	White/Green Stripe & Green
4	White/Orange Stripe & Orange

Outer Jacket Material

Material	Nominal Diameter	Ripcord
PVC - Polyvinyl Chloride	0.365 x 0.165 in	No

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
90 Ohm/km	3 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
49.2 pF/100m	15 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]

100 MHz	537.6 ns/100m	25 ns/100m	70 %
---------	---------------	------------	------

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2.0 dB/100m	74.3 dB	72.3 dB	70.3 dB	70.3 dB	67.8 dB	64.8 dB	20.0 dB	100 ± 12 Ohm	100 ± 15 Ohm
4 MHz	4.1 dB/100m	65.3 dB	63.3 dB	59.2 dB	59.2 dB	55.7 dB	52.8 dB	23.0 dB	100 ± 12 Ohm	100 ± 15 Ohm
8 MHz	5.8 dB/100m	60.3 dB	58.8 dB	53.0 dB	53.0 dB	49.7 dB	46.7 dB	24.5 dB	100 ± 12 Ohm	100 ± 15 Ohm
10 MHz	6.5 dB/100m	59.3 dB	57.3 dB	51.0 dB	51.0 dB	47.8 dB	44.8 dB	25.0 dB	100 ± 12 Ohm	100 ± 15 Ohm
16 MHz	8.2 dB/100m	56.3 dB	54.3 dB	46.0 dB	46.0 dB	43.7 dB	40.7 dB	25.0 dB	100 ± 12 Ohm	100 ± 8 Ohm
20 MHz	9.3 dB/100m	54.8 dB	52.8 dB	43.5 dB	43.5 dB	41.7 dB	38.7 dB	25.0 dB	100 ± 12 Ohm	100 ± 8 Ohm
25 MHz	10.4 dB/100m	53.4 dB	51.4 dB	41.0 dB	42.0 dB	39.8 dB	36.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 8 Ohm
31.25 MHz	11.7 dB/100m	51.9 dB	49.9 dB	38.2 dB	38.2 dB	37.9 dB	34.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 8 Ohm
62.5 MHz	17.0 dB/100m	47.4 dB	45.4 dB	28.4 dB	28.4 dB	31.8 dB	28.9 dB	21.5 dB	100 ± 15 Ohm	100 ± 8 Ohm
100 MHz	22.0 dB/100m	44.3 dB	42.3 dB	25.0 dB	25.0 dB	27.8 dB	24.8 dB	21.0 dB	100 ± 15 Ohm	100 ± 8 Ohm
155 MHz	30.2 dB/100m	41.5 dB	39.5 dB	14.0 dB	14.0 dB	23.9 dB	20.9 dB	21.0 dB	100 ± 15 Ohm	100 ± 8 Ohm
200 MHz	34.8 dB/100m	39.8 dB	37.8 dB	10.0 dB	10.0 dB	21.7 dB	18.8 dB	21.0 dB	100 ± 15 Ohm	100 ± 8 Ohm
250 MHz	39.6 dB/100m	38.3 dB	36.3 dB	3.0 dB	3.0 dB	19.8 dB	16.8 dB	18.0 dB	100 ± 20 Ohm	100 ± 8 Ohm
300 MHz	46.7 dB/100m	37.2 dB	35.2 dB			18.2 dB	15.2 dB	18.0 dB	100 ± 20 Ohm	100 ± 8 Ohm
310 MHz	47.6 dB/100m	36.9 dB	34.9 dB			17.9 dB	14.9 dB	18.0 dB	100 ± 20 Ohm	100 ± 8 Ohm
350 MHz	51.1 dB/100m	36.2 dB	34.2 dB			16.9 dB	13.9 dB	17.0 dB	100 ± 22 Ohm	100 ± 8 Ohm
400 MHz	55.3 dB/100m	35.3 dB	33.3 dB			15.7 dB	12.7 dB	14.0 dB	100 ± 32 Ohm	100 ± 8 Ohm
500 MHz	63.3 dB/100m	33.8 dB	31.8 dB			13.8 dB	10.8 dB	14.0 dB	100 ± 32 Ohm	100 ± 8 Ohm

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Installation Temp Range:	0°C To +50°C
UL Temp Rating:	75°C
Storage Temp Range:	-20°C To +75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	28 lbs/1000ft
Max Recommended Pulling Tension:	40 lbs
Min Bend Radius During Installation:	3.75 in
Min Bend Radius/Minor Axis:	0.5 in

Standards

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMR
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class E Patch
CPR Euroclass:	Eca
Data Category:	Category 6
ANSI Compliance:	S-116-732-2013 Category 6 Patch, ANSI/NEMA WC-66 Category 6 Patch
Telecommunications Standards:	ANSI/TIA-568-C.2 Category 6 Patch
IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Third Party Performance Verification:	Category 6 Patch

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes

EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL 1666 Riser
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length	Footnote
1875GB 0101000	Black	612825125754	1,000 ft	C
1875GB 0061000	Blue	612825125723	1,000 ft	C
1875GB 006A1000	Blue	612825125716	1,000 ft	
1875GB F2V1000	Gray	612825125662	1,000 ft	
1875GB F6H1000	Gray	612825125679	1,000 ft	C
1875GB 0051000	Green	612825125709	1,000 ft	
1875GB 005A1000	Green	612825125693	1,000 ft	
1875GB 007A1000	Purple	612825125730	1,000 ft	
1875GB 0091000	White	612825125747	1,000 ft	
1875GB 0041000	Yellow	612825125686	1,000 ft	C

Footnote:	C - CRATE REEL PUT-UP.
Patent:	https://www.belden.com/resources/patents

Product Notes

Notes:	Values above 350 MHz are information only. Print Includes Descending Footage Markings.
--------	--

History

Update and Revision:	Revision Number: 0.367 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.