



Product: [2107A](#)

Fieldbus, 24 Pr #18 Str TC, XLPO Ins, IS/OS, TPE Jkt, CMG

[Request Sample](#)

Product Description

Fieldbus, 24 Pair 18AWG (7x26) Tinned Copper, XLPO Insulation, Individual & Overall Beldfoil® Shield, TPE Outer Jacket, CMG

Technical Specifications

Product Overview

Suitable Applications:	harsh environment digital and serial two-way communication, oil and gas extraction and refining sites, petrochemical, Profibus process automation or Foundation FieldBus process automation, extreme temperature environments, exposure to humidity/moisture, dust, and oil, remote locations long distance applications, etc.
------------------------	--

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Pairs
Pair(s)	18	7x26	TC - Tinned Copper	24

Conductor Count:	48
Total Number of Pairs:	24

Insulation

Material	Nominal Wall Thickness
XLPE - Cross-Linked Polyethylene (Thermoset)	0.032 in

Color Chart

Number	Color
1	Blue, Orange and Numbered
2	
3	
4	
5	
6	
7	
8	
9	
10	
11	
12	
13	
14	
15	
16	
17	
18	
19	
20	
21	
22	
23	

Inner Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	20

Outer Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	18

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
TPE - Thermoplastic Elastomer	1.389 in	0.085 in

Electrical Characteristics**Conductor DCR**

Nominal Conductor DCR
5.86 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
22 pF/ft

Inductance

Nominal Inductance
0.22 μ H/ft

Impedance

Nominal Characteristic Impedance
100 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
0.039 MHz	0.08 dB/100ft

Delay

Nominal Velocity of Propagation (VP) [%]
64%

Current

Max. Recommended Current [A]
5.4 Amps per Conductor

Voltage

UL Voltage Rating
300 V RMS

Electrical Characteristics Notes:	Max Propagation Delay Change From 7.812 kHz to 39.06 kHz: 518 pS/ft
Other Electrical Characteristic 2:	31.25 KBits/sec

Temperature Range

UL Temp Rating:	90°C
Operating Temperature Range:	-40°C to 90°C

Mechanical Characteristics

Oil Resistance:	Yes
Bulk Cable Weight:	797 lbs/1000ft
Max. Pull Tension:	1400 lbs
Min. Bend Radius/Minor Axis:	14.0 in

Standards

NEC Articles:	Article 725, Article 727, Article 800
NEC/(UL) Compliance:	CMG, ITC, PLTC-ER

CEC/C(UL) Compliance:	CIC, TC
CSA AWM Compliance:	AWM I A/B II A/B
ISO/IEC Compliance:	IEC 61158-2
Other Standards:	ISA/SP-50 Type A

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
IEC Flammability:	IEC 60332-3-24
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	UPC
2107A 0061000	Blue, Light	612825129103
2107A 0031000	Orange	612825129097

History

Update and Revision:	Revision Number: 0.465 Revision Date: 11-15-2024
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.