



**Product:** [2119A](#)

Fieldbus, 2 Pr #18 Str TC, XLPO Ins, IS/OS, TPE Jkt, 600V TC-ER

[Request Sample](#)

## Product Description

Fieldbus, 2 Pair 18AWG (7x26) Tinned Copper, XLPO Insulation, Individual & Overall Beldfoil® Shield, Orange TPE Outer Jacket, 600V TC-ER

## Technical Specifications

### Product Overview

Suitable Applications:	harsh environment digital and serial two-way communication, oil and gas extraction and refining sites, petrochemical, Profibus process automation or Foundation FieldBus process automation, extreme temperature environments, exposure to humidity/moisture, dust, and oil, remote locations long distance applications, etc.
------------------------	--

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
18	7x26	TC - Tinned Copper	2

Conductor Count:	4
------------------	---

#### Insulation

Material	Nominal Wall Thickness
XLPE - Cross-Linked Polyethylene (Thermoset)	0.032 in

#### Color Chart

Number	Color
1	Blue, Orange and Numbered
2	

#### Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	20	7x28

#### Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	18	7x26

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
TPE - Thermoplastic Elastomer	0.512 in	0.047 in	Yes

### Electrical Characteristics

#### Conductor DCR

<b>Nominal Conductor DCR</b>
5.86 Ohm/1000ft

#### Capacitance

Max. Capacitance Unbalance	Nom. Capacitance Conductor to Conductor
1.2 pF/ft	22 pF/ft

## Inductance

### Nominal Inductance

0.22 µH/ft

## Impedance

### Nominal Characteristic Impedance

100 Ohm

## High Frequency (Nominal/Typical)

### Frequency [MHz] | Nom. Insertion Loss

0.039 MHz | 0.08 dB/100ft

## High Freq

### Max. Insertion Loss (Attenuation) | Max./Min. Input Impedance (unFitted)

0.091 dB/100ft | 100 Ohm

## Current

### Element | Max. Recommended Current [A]

Per Conductor | 8.7 Amps per Conductor

## Voltage

### Description | UL Voltage Rating

CSA CIC type TC | 600 V

Electrical Characteristics Notes: Max Propagation Delay Change From 7.812 kHz to 39.06 kHz: 518 pS/ft

Other Electrical Characteristic 2: 31.25 KBits/sec

## Temperature Range

UL Temp Rating: 90°C

Operating Temp Range: -40°C to 90°C

## Mechanical Characteristics

Oil Resistance: Yes

Bulk Cable Weight: 109 lbs/1000ft

Max. Pull Tension: 137 lbs

Min Bend Radius/Minor Axis: 5.25 in

## Standards

NEC Articles: Article 336

NEC/(UL) Compliance: TC-ER

CSA AWM Compliance: AWM I A/B II A/B

IEC Compliance: IEC 61158-2

Other Compliance: ISA/SP-50 Type A

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2003/11/EC (BFR): Yes

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2012/19/EU (WEEE): Yes

EU Directive 2015/863/EU: Yes

EU Directive Compliance: EU Directive 2003/11/EC (BFR)

EU CE Mark: Yes

MII Order #39 (China RoHS): Yes

## Suitability

Suitability - Burial: Yes

Suitability - Indoor:	Yes
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

## Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1581 Vertical Tray
CSA Flammability:	FT4
IEC Flammability:	60332-3-24 (Category C)
UL voltage rating:	600 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
2119A 0061000	Blue, Light	Reel	1,000 ft	612825129530
2119A 0065000	Blue, Light	Reel	5,000 ft	612825129547
2119A 0031000	Orange	Reel	1,000 ft	612825129516
2119A 0035000	Orange	Reel	5,000 ft	612825129523

## History

Update and Revision:	Revision Number: 0.351 Revision Date: 02-16-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.